

Leap

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020

ALSO IN

Bath
Close-to-Ceiling

PAIR WITH

Wisten
Joy

SEMI-FLUSH CONVERTIBLE

P350060-009 Brushed Nickel
Hanging and ceiling mount hardware included.
14" W., 8-7/8" ht.,
Overall ht. w/stem 47"; wire 10'.
Two medium base lamps, each 100w max.

THREE-LIGHT CHANDELIER

P400042-009 Brushed Nickel
21" dia., 27-5/8" ht.,
Overall ht. w/chain 102"; wire 15'.
Three medium base lamps, each 100w max.

FIVE-LIGHT CHANDELIER

P400043-009 Brushed Nickel
25" dia., 30" ht.,
Overall ht. w/chain 105"; wire 15'.
Five medium base lamps, each 100w max.

NINE-LIGHT CHANDELIER

P400044-009 Brushed Nickel
26-3/8" dia., 37" ht.,
Overall ht. w/chain 160"; wire 15'.
Nine medium base lamps, each 100w max.

MINI-PENDANT

P500029-009 Brushed Nickel
5" dia., 6-1/2" ht.,
Overall ht. w/stem 72-1/2"; wire 10'.
One medium base lamp, 100w max.

THREE-LIGHT PENDANT

P500030-009 Brushed Nickel
18" dia., 21" ht.,
Overall ht. w/chain 87"; wire 10'.
Three medium base lamps, each 100w max.



P400043-009



P400044-009



P400044-020



P400043-020



P400042-009



P500030-009



P500030-020



P400042-020



P500029-009



P500030-009

shown hanging



P350060-020

shown hanging



P500029-020

Leap

SEMI-FLUSH CONVERTIBLE

P350060-020 Antique Bronze
Hanging and ceiling mount hardware included.
14" W., 8-7/8" ht.,
Overall ht. w/stem 47"; wire 10'.
Two medium base lamps, each 100w max.

THREE-LIGHT CHANDELIER

P400042-020 Antique Bronze
21" dia., 27-5/8" ht.,
Overall ht. w/chain 102"; wire 15'.
Three medium base lamps, each 100w max.

FIVE-LIGHT CHANDELIER

P400043-020 Antique Bronze
25" dia., 30" ht.,
Overall ht. w/chain 105"; wire 15'.
Five medium base lamps, each 100w max.

NINE-LIGHT CHANDELIER

P400044-020 Antique Bronze
26-3/8" dia., 37" ht.,
Overall ht. w/chain 160"; wire 15'.
Nine medium base lamps, each 100w max.

MINI-PENDANT

P500029-020 Antique Bronze
5" dia., 6-1/2" ht.,
Overall ht. w/stem 72-1/2"; wire 10'.
One medium base lamp, 100w max.

THREE-LIGHT PENDANT

P500030-020 Antique Bronze
18" dia., 21" ht.,
Overall ht. w/chain 87"; wire 10'.
Three medium base lamps, each 100w max.

Leap

Leap vanity fixtures feature tapered etched glass shades to complement contemporary design trends.

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020

ALSO IN

Collections
Close-to-Ceiling

ONE-LIGHT BATH

P300131-009 Brushed Nickel
P300131-020 Antique Bronze
5" W., 8-1/8" ht.
Extends 6-1/8". H/CTR 4-1/4".
One medium base lamp,
100w max.

TWO-LIGHT BATH

P300132-009 Brushed Nickel
P300132-020 Antique Bronze
13-7/8" W., 8-3/8" ht.
Extends 6-1/8". H/CTR 6".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH

P300133-009 Brushed Nickel
P300133-020 Antique Bronze
22-7/8" W., 8-3/8" ht.
Extends 6-1/8". H/CTR 6".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH

P300134-009 Brushed Nickel
P300134-020 Antique Bronze
31-3/4" W., 8-3/8" ht.
Extends 6-1/8". H/CTR 6".
Four medium base lamps,
each 100w max.

All fixtures mount up or down.



P300131-009



P300132-009



P300133-009



P300134-009



P300131-020



P300132-020



P300133-020



P300134-020

Leap

Large-scale, tapered etched glass shades perfectly complement contemporary design.



P350060-009



P350060-020



P350061-009



P350061-020

SEMI-FLUSH CONVERTIBLE

P350060-009 Brushed Nickel
P350060-020 Antique Bronze
Hanging and ceiling mount hardware included.
14" dia., 8-7/8" ht.,
Overall ht. w/chain 47"; wire 10'.
Two medium base lamps, each 100w max.

TWO-LIGHT FLUSH MOUNT

P350061-009 Brushed Nickel
P350061-020 Antique Bronze
14" dia., 6-5/8" ht.
Two medium base lamps, each 60w max.