

Bravo

FINISH

- Brushed Nickel - 09 Joy
- Antique Bronze - 20W Mingle

PAIR WITH

WALL BRACKET

P2004-09 Brushed Nickel
7-1/4" W., 9" ht.,
Extends 8-3/4". H/CTR 4-1/2".
One medium base lamp, 100w max.

THREE-LIGHT FOYER

P3821-09 Brushed Nickel
18" dia., 21-1/2" ht.,
Overall ht. w/chain 96"; wire 12'.
Three candelabra base lamps,
each 60w max.

THREE-LIGHT PENDANT

P3912-09 Brushed Nickel
21" dia., 23-1/2" ht.,
Overall ht. w/chain 98"; wire 12'.
Three medium base lamps,
each 100w max.

THREE-LIGHT FOYER

P3969-09 Brushed Nickel
20" dia., 30-3/8" ht.,
Overall ht. w/chain 105"; wire 12'.
Three medium base lamps,
each 100w max.

THREE-LIGHT CHANDELIER

P4621-09 Brushed Nickel
23" dia., 20-1/8" ht.,
Overall ht. w/chain 95"; wire 12'.
Three medium base lamps,
each 100w max.

FOUR-LIGHT CHANDELIER

P4622-09 Brushed Nickel
24" dia., 21" ht.,
Overall ht. w/chain 96"; wire 12'.
Four medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER

P4623-09 Brushed Nickel
27" dia., 23" ht.,
Overall ht. w/chain 97"; wire 12'.
Five medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER

P4625-09 Brushed Nickel
32" dia., 31" ht.,
Overall ht. w/chain 106"; wire 15'.
Nine medium base lamps,
each 100w max.

TWELVE-LIGHT CHANDELIER

P4687-09 Brushed Nickel
38" W., 44" ht.,
Overall ht. w/chain 119"; wire 15'.
Twelve medium base lamps,
each 100w max.

MINI-PENDANT

P5300-09 Brushed Nickel
7-1/4" dia., 6-1/2" ht.,
Overall ht. w/chain or stem 94"; wire 10'.
One medium base lamp, 100w max.



Bravo

WALL BRACKET

P2004-20W Antique Bronze
7-1/4" W., 9" ht.,
Extends 8-3/4". H/CTR 4-1/2".
One medium base lamp, 100w max.

THREE-LIGHT FOYER

P3821-20W Antique Bronze
18" dia., 21-1/2" ht.,
Overall ht. w/chain 96"; wire 12'.
Three candelabra base lamps,
each 60w max.

THREE-LIGHT PENDANT

P3912-20W Antique Bronze
21" dia., 23-1/2" ht.,
Overall ht. w/chain 98"; wire 12'.
Three medium base lamps,
each 100w max.

THREE-LIGHT FOYER

P3969-20W Antique Bronze
20" dia., 30-3/8" ht.,
Overall ht. w/chain 105-1/2"; wire 12'.
Three medium base lamps,
each 100w max.

THREE-LIGHT CHANDELIER

P4621-20W Antique Bronze
23" dia., 20-1/8" ht.,
Overall ht. w/chain 95"; wire 12'.
Three medium base lamps,
each 100w max.

FOUR-LIGHT CHANDELIER

P4622-20W Antique Bronze
24" dia., 21" ht.,
Overall ht. w/chain 96"; wire 12'.
Four medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER

P4623-20W Antique Bronze
27" dia., 23" ht.,
Overall ht. w/chain 97"; wire 12'.
Five medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER

P4625-20W Antique Bronze
32" dia., 31" ht.,
Overall ht. w/chain 106"; wire 15'.
Nine medium base lamps,
each 100w max.

TWELVE-LIGHT CHANDELIER

P4687-20W Antique Bronze
38" dia., 44" ht.,
Overall ht. w/chain 119"; wire 15'.
Twelve medium base lamps,
each 75w max.

MINI-PENDANT

P5300-20W Antique Bronze
7-1/4" dia., 6-1/2" ht.,
Overall ht. w/chain or stem 94"; wire 10'.
One medium base lamp, 100w max.

Bravo

A current, truly transitional style is achieved with Bravo's free flowing arms that are gracefully suspended with fluted shaped glass. The popular Bravo collection comes with etched linen glass.

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

ALSO IN

Collections
Close-to-Ceiling

ONE-LIGHT BATH

P2004-09 Brushed Nickel
P2004-20W Antique Bronze
7-1/4" W., 9" ht.
Extends 8-3/4". H/CTR 4-1/2".
One medium base lamp,
100w max.

TWO-LIGHT BATH

P2005-09 Brushed Nickel
P2005-20W Antique Bronze
17" W., 8-1/2" ht.
Extends 8-3/4". H/CTR 6".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH

P2006-09 Brushed Nickel
P2006-20W Antique Bronze
26-3/4" W., 8-3/4" ht.
Extends 8-3/4". H/CTR 6".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH

P2007-09 Brushed Nickel
P2007-20W Antique Bronze
37-1/4" W., 8-3/4" ht.
Extends 8-3/4". H/CTR 6".
Four medium base lamps,
each 100w max.

FIVE-LIGHT BATH

P2016-09 Brushed Nickel
P2016-20W Antique Bronze
46-1/4" W., 8-7/8" ht.
Extends 8-3/4". H/CTR 6-3/8".
Five medium base lamps,
each 100w max.

All fixtures mount up or down.

