

Arden

FINISH

- Brushed Nickel - 09
- Antique Bronze - 20

ALSO IN

Bath
Close-to-Ceiling

PAIR WITH

Drum Shade
Piedmont

WALL BRACKET

P2127-09 Brushed Nickel
5-7/8" W., 8" ht.,
Extends 8-1/4". H/CTR 4".
One medium base lamp,
100w max.

SEMI-FLUSH CONVERTIBLE

P3720-09 Brushed Nickel
Hanging and ceiling mount
hardware included.
14" dia., 11-3/8" ht.,
Overall ht. w/chain 50"; wire 10'.
Two medium base lamps,
each 100w max.

THREE-LIGHT PENDANT

P3905-09 Brushed Nickel
18-1/8" dia., 24-5/8" ht.,
Overall ht. w/stem 99"; wire 10'.
Three medium base lamps,
each 100w max.

THREE-LIGHT CHANDELIER

P4745-09 Brushed Nickel
22" dia., 18-3/4" ht.,
Overall ht. w/chain 93"; wire 15'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER

P4746-09 Brushed Nickel
24-5/8" dia., 22-1/4" ht.,
Overall ht. w/chain 97"; wire 15'.
Five medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER

P4747-09 Brushed Nickel
30-1/2" dia., 30" ht.,
Overall ht. w/chain 153"; wire 15'.
Nine medium base lamps,
each 100w max.

TWELVE-LIGHT CHANDELIER

P4748-09 Brushed Nickel
42" dia., 41-1/2" ht.,
Overall ht. w/chain 164"; wire 15'.
Twelve medium base lamps,
each 75w max.

MINI-PENDANT

P5092-09 Brushed Nickel
5-7/8" dia., 9-5/8" ht.,
Overall ht. w/chain 75-1/2"; wire 10'.
One medium base lamp, 100w max.



P4745-09



P3720-09
shown as hanging



P3905-09



P5092-09



P2127-09



P4748-09



P4747-09



P4746-09



P4748-20



P4747-20



P4746-20



P4745-20



P3720-20
shown as hanging



P3905-20



P5092-20



P2127-20

Arden

WALL BRACKET

P2127-20 Antique Bronze
5-7/8" W., 8" ht.,
Extends 8-1/4". H/CTR 4".
One medium base lamp,
100w max.

SEMI-FLUSH CONVERTIBLE

P3720-20 Antique Bronze
Hanging and ceiling mount
hardware included.
14" dia., 11-3/8" ht.,
Overall ht. w/chain 50"; wire 10'.
Two medium base lamps,
each 100w max.

THREE-LIGHT PENDANT

P3905-20 Antique Bronze
18-1/8" dia., 24-5/8" ht.,
Overall ht. w/stem 99"; wire 10'.
Three medium base lamps,
each 100w max.

THREE-LIGHT CHANDELIER

P4745-20 Antique Bronze
22" dia., 18-3/4" ht.,
Overall ht. w/chain 93"; wire 15'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER

P4746-20 Antique Bronze
24-5/8" dia., 22-1/4" ht.,
Overall ht. w/chain 97"; wire 15'.
Five medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER

P4747-20 Antique Bronze
30-1/2" dia., 30" ht.,
Overall ht. w/chain 153"; wire 15'.
Nine medium base lamps,
each 100w max.

TWELVE-LIGHT CHANDELIER

P4748-20 Antique Bronze
42" dia., 41-1/2" ht.,
Overall ht. w/chain 164"; wire 15'.
Twelve medium base lamps,
each 75w max.

MINI-PENDANT

P5092-20 Antique Bronze
5-7/8" dia., 9-5/8" ht.,
Overall ht. w/chain 75-1/2"; wire 10'.
One medium base lamp,
100w max.

Arden

Arden features updated farmhouse styling to complement casual home styles.

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

ALSO IN

Collections
Close-to-Ceiling



P2128-09



P2127-09



P2129-09



P2130-09



P2128-20



P2127-20



P2129-20



P2130-20

ONE-LIGHT BATH

P2127-09 Brushed Nickel

P2127-20 Antique Bronze

5-7/8" W., 8" ht.

Extends 8-1/4". H/CTR 4".

One medium base lamp,

100w max.

TWO-LIGHT BATH

P2128-09 Brushed Nickel

P2128-20 Antique Bronze

16-1/2" W., 7-1/2" ht.

Extends 8-1/8". H/CTR 4-5/8".

Two medium base lamps,

each 100w max.

THREE-LIGHT BATH

P2129-09 Brushed Nickel

P2129-20 Antique Bronze

24-1/2" W., 7-1/2" ht.

Extends 8-1/4". H/CTR 4-5/8".

Three medium base lamps,

each 100w max.

FOUR-LIGHT BATH

P2130-09 Brushed Nickel

P2130-20 Antique Bronze

34" W., 7-1/2" ht.

Extends 8-1/4". H/CTR 4-5/8".

Four medium base lamps,

each 100w max.

All fixtures mount up or down.

Arden

Summer linen shades with etched glass diffuser.



P3720-20



P3720-09



P3739-20



P3739-09

SEMI-FLUSH CONVERTIBLE

P3720-09 Brushed Nickel

P3720-20 Antique Bronze

Hanging and ceiling mount hardware included.

14" dia., 11-3/8" ht.,

Overall ht. w/chain 50"; wire 10'.

Two medium base lamps,

each 100w max.

TWO-LIGHT FLUSH MOUNT

P3739-09 Brushed Nickel

P3739-20 Antique Bronze

14" dia., 6-5/8" ht.

Two medium base lamps,

each 60w max.