

Madison

FINISH

- Brushed Nickel - 09
- Antique Bronze - 20

ALSO IN

Bath
Close-to-Ceiling
Ceiling Fan

PAIR WITH

Hansford
Drum Shade

WALL BRACKET

P3161-09 Brushed Nickel
7-5/8" W., 8" ht.,
Extends 8-1/2". H/CTR 5".
One medium base lamp,
100w max.

SEMI-FLUSH CONVERTIBLE

P3792-09 Brushed Nickel
Hanging and ceiling mount
hardware included.
9-1/2" dia., 14-5/8" ht.,
Overall ht. w/chain 90"; wire 15'.
One medium base lamp,
75w max.

ONE-LIGHT PENDANT

P3793-09 Brushed Nickel
11" dia., 21-3/8" ht.,
Overall ht. w/chain 96"; wire 15'.
One medium base lamp,
100w max.

THREE-LIGHT CHANDELIER

P4280-09 Brushed Nickel
22" dia., 20" ht.,
Overall ht. w/chain 95"; wire 15'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER

P4281-09 Brushed Nickel
24-5/8" dia., 25" ht.,
Overall ht. w/chain 100"; wire 15'.
Five medium base lamps,
each 100w max.

THREE-LIGHT LINEAR CHANDELIER

P4282-09 Brushed Nickel
31-1/4" W., 7-5/8" D., 24" ht.,
Overall ht. w/chain 99"; wire 15'.
Three medium base lamps,
each 100w max.

MINI-PENDANT

P5078-09 Brushed Nickel
7-1/2" dia., 8" ht.,
Overall ht. w/stem 52"; wire 10'.
One medium base lamp,
100w max.



P4282-09
shown with glass
facing down



P4282-20
shown with glass
facing down



P3792-09



P4281-09
shown with glass
facing up



P4281-20
shown with glass
facing down



P3792-20



P3793-09



P4280-09
shown with glass
facing down



P4280-20
shown with glass
facing up



P3793-20



P5078-09



P3161-09



P3161-20



P5078-20

Madison

WALL BRACKET

P3161-20 Antique Bronze
7-5/8" W., 8" ht.,
Extends 8-1/2". H/CTR 5".
One medium base lamp,
100w max.

SEMI-FLUSH CONVERTIBLE

P3792-20 Antique Bronze
Hanging and ceiling mount
hardware included.
9-1/2" dia., 14-5/8" ht.,
Overall ht. w/chain 90"; wire 15'.
One medium base lamp,
75w max.

ONE-LIGHT PENDANT

P3793-20 Antique Bronze
11" dia., 21-3/8" ht.,
Overall ht. w/chain 96"; wire 15'.
One medium base lamp,
100w max.

THREE-LIGHT CHANDELIER

P4280-20 Antique Bronze
22" dia., 20" ht.,
Overall ht. w/chain 95"; wire 15'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER

P4281-20 Antique Bronze
24-5/8" dia., 25" ht.,
Overall ht. w/chain 100"; wire 15'.
Five medium base lamps,
each 100w max.

THREE-LIGHT LINEAR CHANDELIER

P4282-20 Antique Bronze
31-1/4" W., 7-5/8" D., 24" ht.,
Overall ht. w/chain 99"; wire 15'.
Three medium base lamps,
each 100w max.

MINI-PENDANT

P5078-20 Antique Bronze
7-1/2" dia., 8" ht.,
Overall ht. w/stem 52"; wire 10'.
One medium base lamp,
100w max.

Madison

Authentic and handsome details represent a throwback to a simpler time. Etched glass shade offers classic styling.



P3164-09

P3161-09

FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15
- Antique Bronze - 20

ALSO IN

Collections
Close-to-Ceiling



P3162-09

P3163-09

ONE-LIGHT BATH

P3161-09 Brushed Nickel
P3161-15 Polished Chrome
P3161-20 Antique Bronze
7-5/8" W., 8" ht.
Extends 9-1/4". H/CTR 5"
One medium base lamp,
100w max.



P3164-20

P3161-20

TWO-LIGHT BATH

P3162-09 Brushed Nickel
P3162-15 Polished Chrome
P3162-20 Antique Bronze
17-1/2" W., 8" ht.
Extends 8-3/4". H/CTR 4-7/8"
Two medium base lamps,
each 100w max.



P3162-20

P3163-20

THREE-LIGHT BATH

P3163-09 Brushed Nickel
P3163-15 Polished Chrome
P3163-20 Antique Bronze
27-1/2" W., 8" ht.
Extends 8-3/4". H/CTR 4-7/8"
Three medium base lamps,
each 100w max.



P3164-15

P3161-15

FOUR-LIGHT BATH

P3164-09 Brushed Nickel
P3164-15 Polished Chrome
P3164-20 Antique Bronze
37-1/2" W., 8" ht.
Extends 9-3/4". H/CTR 4-7/8"
Four medium base lamps,
each 100w max.



P3162-15

P3163-15

All fixtures mount up or down.

Madison

Etched glass and transitional elements offer a simplified vintage style.



ONE-LIGHT FLUSH MOUNT

P3311-09 Brushed Nickel

P3311-20 Antique Bronze

12" dia., 7-1/2" ht.

One medium base lamp,
60w max.

TWO-LIGHT FLUSH MOUNT

P3312-09 Brushed Nickel

P3312-20 Antique Bronze

15-3/4" dia., 8-1/4" ht.

Two medium base lamps,
each 60w max.



THREE-LIGHT SEMI-FLUSH

P3663-09 Brushed Nickel

P3663-20 Antique Bronze

Glass reverses up or down.
20-3/4" dia., 14" ht.

Three medium base lamps,
each 60w max.

