

Riley

FINISHES

- Brushed Nickel - 009
- Matte Black - 031

ALSO IN

Bath
Sconces

PAIR WITH

Landree
Draper

FIVE-LIGHT CHANDELIER

P400209-009 Brushed Nickel
24" dia., 19-3/4" ht.,
Overall ht. w/chain 85-1/2", wire 15'.
Five candelabra base lamps,
each 60w max.

NINE-LIGHT CHANDELIER

P400210-009 Brushed Nickel
30" dia., 25-1/8" ht.,
Overall ht. w/chain 91", wire 15'.
Nine candelabra base lamps,
each 60w max.

THREE-LIGHT PENDANT

P500243-009 Brushed Nickel
21" dia., 11" ht.,
Overall ht. w/chain 77", wire 15'.
Three candelabra base lamps,
each 60w max.

WALL BRACKET

P710082-009 Brushed Nickel
5" W., 14-1/2" ht.,
Extends 4-5/8". H/CTR 7-3/4".
One candelabra base lamp,
60w max.

*All fixtures shown with EF4T8D927/JA8
LED lamps, not included.*



P400210-009



P400209-009



P500243-009



P710082-009



P400210-031



P400209-031



P500243-031



P710082-031

Riley

FIVE-LIGHT CHANDELIER

P400209-031 Matte Black
24" dia., 19-3/4" ht.,
Overall ht. w/chain 85-1/2", wire 15'.
Five candelabra base lamps,
each 60w max.

NINE-LIGHT CHANDELIER

P400210-031 Matte Black
30" dia., 25-1/8" ht.,
Overall ht. w/chain 91", wire 15'.
Nine candelabra base lamps,
each 60w max.

THREE-LIGHT PENDANT

P500243-031 Matte Black
21" dia., 11" ht.,
Overall ht. w/chain 77", wire 15'.
Three candelabra base lamps,
each 60w max.

WALL BRACKET

P710082-031 Matte Black
5" W., 14-1/2" ht.,
Extends 4-5/8". H/CTR 7-3/4".
One candelabra base lamp,
60w max.

*All fixtures shown with EF4T8D927/JA8
LED lamps, not included.*

Riley



P300277-009



P710082-009



P300278-009



P300279-009



P300277-031



P710082-031



P300278-0031



P300279-031

Smooth metal arms extend from an oval backplate to hold simple light bases topped with elegant, elongated clear glass shades.

FINISHES

- Brushed Nickel - 009
- Black - 031

ALSO IN

Collections

TWO-LIGHT BATH

P300277-009 Brushed Nickel

P300277-031 Black

16-1/8" W., 8-1/4" ht.

Extends 5-1/2". H/CTR 5-3/4".

Two medium base lamps, each 60w max.

THREE-LIGHT BATH

P300278-009 Brushed Nickel

P300278-031 Black

25-1/4" W., 8-1/4" ht.

Extends 5-1/2". H/CTR 5-3/4".

Three medium base lamps, each 60w max.

FOUR-LIGHT BATH

P300279-009 Brushed Nickel

P300279-031 Black

34-3/8" W., 8-1/4" ht.

Extends 5-1/2". H/CTR 5-3/4".

Four medium base lamps, each 60w max.

WALL BRACKET

P710082-009 Brushed Nickel

P710082-031 Black

5" W., 14-1/2" ht.

Extends 4-5/8". H/CTR 7-3/4".

One candelabra base lamp, 60w max.

All fixtures mount up or down, except P710082.

Shown with P7825-01 vintage lamps, not included. See page 824.

Riley

Smooth metal arms hold simple light bases topped with elegant, elongated clear glass shades.

P710082-009 Brushed Nickel

P710082-031 Black

5" W., 14-1/2" ht.

Extends 4-5/8". H/CTR 7-3/4".

One candelabra base lamp,
60w max.

*Fixture shown with P7826-01
vintage lamp.*



P710082-009



P710082-031