

Heart

FINISH

- Brushed Nickel - 09
- Antique Bronze - 20

ALSO IN

Bath

PAIR WITH

Laird
Trinity
Five-Light

WALL BRACKET

P2913-09 Brushed Nickel
6" W., 9-1/16" ht.,
Extends 8". H/CTR 4-1/2".
One medium base lamp,
100w max.

THREE-LIGHT PENDANT

P3955-09 Brushed Nickel
17-3/4" dia., 21-3/4" ht.,
Overall ht. w/chain 66"; wire 8'.
Three medium base lamps,
each 100w max.

THREE-LIGHT CHANDELIER

P4664-09 Brushed Nickel
22" dia., 18" ht.,
Overall ht. w/chain 63"; wire 8'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER

P4666-09 Brushed Nickel
25-1/2" dia., 19-1/8" ht.,
Overall ht. w/chain 63"; wire 8'.
Five medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER

P4668-09 Brushed Nickel
30" dia., 27-3/4" ht.,
Overall ht. w/chain 90"; wire 12'.
Nine medium base lamps,
each 100w max.

MINI-PENDANT

P5131-09 Brushed Nickel
6" dia., 6" ht., Overall ht.
w/chain or stem 63"; wire 8'.
One medium base lamp,
100w max.



P3955-09



P4668-09



P4668-20



P3955-20



P4664-09



P4666-09



P4666-20



P4664-20



P2913-09



P5131-09



P5131-20



P2913-20

Heart

WALL BRACKET

P2913-20 Antique Bronze
6" W., 9-1/16" ht.,
Extends 8". H/CTR 4-1/2".
One medium base lamp,
100w max.

THREE-LIGHT PENDANT

P3955-20 Antique Bronze
17-3/4" dia., 21-3/4" ht.,
Overall ht. w/chain 66"; wire 8'.
Three medium base lamps,
each 100w max.

THREE-LIGHT CHANDELIER

P4664-20 Antique Bronze
22" dia., 18" ht.,
Overall ht. w/chain 63"; wire 8'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER

P4666-20 Antique Bronze
25-1/2" dia., 19-1/8" ht.,
Overall ht. w/chain 63"; wire 8'.
Five medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER

P4668-20 Antique Bronze
30" dia., 27-3/4" ht.,
Overall ht. w/chain 90"; wire 12'.
Nine medium base lamps,
each 100w max.

MINI-PENDANT

P5131-20 Antique Bronze
6" dia., 6" ht., Overall ht.
w/chain or stem 63"; wire 8'.
One medium base lamp,
100w max.

Heart

Heart will bring romance to the vanity, with flowing arms that gently cradle etched glass bowls.



FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15
- Antique Bronze - 20

ALSO IN

Collections



ONE-LIGHT BATH

P2913-09 Brushed Nickel
P2913-15 Polished Chrome
P2913-20 Antique Bronze
 6" W., 9-1/16" ht.
 Extends 8". H/CTR 4-1/2".
 One medium base lamp,
 100w max.



TWO-LIGHT BATH

P2915-09 Brushed Nickel
P2915-15 Polished Chrome
P2915-20 Antique Bronze
 14" W., 8-3/8" ht.
 Extends 8". H/CTR 2-1/2".
 Two medium base lamps,
 each 100w max.



THREE-LIGHT BATH

P2919-09 Brushed Nickel
P2919-15 Polished Chrome
P2919-20 Antique Bronze
 22" W., 8-1/2" ht.
 Extends 8". H/CTR 2-1/2".
 Three medium base lamps,
 each 100w max.



FOUR-LIGHT BATH

P2928-09 Brushed Nickel
P2928-15 Polished Chrome
P2928-20 Antique Bronze
 29-7/8" W., 8-1/2" ht.
 Extends 8". H/CTR 2-1/2".
 Four medium base lamps,
 each 100w max.



All fixtures mount up or down.