

Apogee LED

FINISH

- Brushed Nickel - 009
- Architectural Bronze - 129

ALSO IN

Close-to-Ceiling

PAIR WITH

Avant
Globe LED

SEMI-FLUSH CONVERTIBLE

P350064-009-30 Brushed Nickel
Hanging and ceiling mount hardware included.
15" dia., 10-3/4" ht.,
Overall ht. w/chain 85-1/4, wire 15'.
30w integrated LED, 3000K,
90CRI, 1855 delivered lumens,
120-277V, 0-10V dimming.

SEMI-FLUSH CONVERTIBLE

P350065-009-30 Brushed Nickel
Hanging and ceiling mount hardware included.
21" dia., 14-1/2" ht.,
Overall ht. w/chain 92", wire 15'.
45w integrated LED, 3000K,
90CRI, 2765 delivered lumens,
120-277V, 0-10V dimming.

SEMI-FLUSH CONVERTIBLE

P350066-009-30 Brushed Nickel
Hanging and ceiling mount hardware included.
27" dia., 20-5/8" ht.,
Overall ht. w/chain 98, wire 15'.
71w integrated LED, 3000K,
90CRI, 4215 delivered lumens,
120-277V, 0-10V dimming.

WALL SCONCE

P710036-009-30 Brushed Nickel
15" W., 7-1/2" ht.,
3-11/16" extends or depth.
20w integrated LED, 3000K,
90CRI, 940 delivered lumens,
120-277V, 0-10V dimming.



All fixtures:



P350066-009-30



P350066-129-30



P350064-009-30
shown hanging



P350065-009-30



P350065-129-30



P350064-129-30
shown hanging



P350064-009-30
shown as ceiling mount



P710036-009-30



P710036-129-30



P350064-129-30
shown as ceiling mount

Apogee LED

SEMI-FLUSH CONVERTIBLE

P350064-129-30 Architectural Bronze
Hanging and ceiling mount hardware included.
15" dia., 10-3/4" ht.,
Overall ht. w/chain 85-1/4, wire 15'.
30w integrated LED, 3000K,
90CRI, 1855 delivered lumens,
120-277V, 0-10V dimming.

SEMI-FLUSH CONVERTIBLE

P350065-129-30 Architectural Bronze
Hanging and ceiling mount hardware included.
21" dia., 14-1/2" ht.,
Overall ht. w/chain 92", wire 15'.
45w integrated LED, 3000K,
90CRI, 2765 delivered lumens,
120-277V, 0-10V dimming.

SEMI-FLUSH CONVERTIBLE

P350066-129-30 Architectural Bronze
Hanging and ceiling mount hardware included.
27" dia., 20-5/8" ht.,
Overall ht. w/chain 98, wire 15'.
90CRI, 4215 delivered lumens,
120-277V, 0-10V dimming.

WALL SCONCE

P710036-129-30 Architectural Bronze
15" W., 7-1/2" ht.,
Extends 3-11/16".
20w integrated LED, 3000K,
90CRI, 940 delivered lumens,
120-277V, 0-10V dimming.



All fixtures:



Apogee LED

Tiered metal banded trim holds etched glass shade providing an even, pleasing light effect.

SEMI-FLUSH CONVERTIBLE

P350064-009-30 Brushed Nickel
P350064-129-30 Architectural Bronze
 Hanging and ceiling mount hardware included.
 15" dia., 10-3/4" ht.,
 Overall ht. w/chain 85-1/4, wire 15'.
 30w integrated LED, 3000K,
 90CRI, 1855 delivered lumens,
 120-277V, 0-10V dimming.



P350066-129-30



P350066-009-30

SEMI-FLUSH CONVERTIBLE

P350065-009-30 Brushed Nickel
P350065-129-30 Architectural Bronze
 Hanging and ceiling mount hardware included.
 21" dia., 14-1/2" ht.,
 Overall ht. w/chain 92", wire 15'.
 45w integrated LED, 3000K,
 90CRI, 2765 delivered lumens,
 120-277V, 0-10V dimming.



P350065-129-30



P350065-009-30

SEMI-FLUSH CONVERTIBLE

P350066-009-30 Brushed Nickel
P350066-129-30 Architectural Bronze
 Hanging and ceiling mount hardware included.
 27" dia., 20-5/8" ht.,
 Overall ht. w/chain 98, wire 15'.
 71w integrated LED, 3000K,
 90CRI, 4215 delivered lumens,
 120-277V, 0-10V dimming.



P350064-129-30



P350064-009-30

FLUSH MOUNT

P350070-009-30 Brushed Nickel
P350070-129-30 Architectural Bronze
 15" dia., 3-11/16" ht.
 30w integrated LED, 3000K,
 90CRI, 1660 delivered lumens,
 120-277V, 0-10V dimming.



P350070-129-30



P350070-129-30

FLUSH MOUNT

P350071-009-30 Brushed Nickel
P350071-129-30 Architectural Bronze
 21" dia., 4-1/2" ht.
 45w integrated LED, 3000K,
 90CRI, 2550 delivered lumens,
 120-277V, 0-10V dimming.



P350071-129-30



P350071-129-30

FLUSH MOUNT

P350072-009-30 Brushed Nickel
P350072-129-30 Architectural Bronze
 27" dia., 5-3/8" ht.
 71w integrated LED, 3000K,
 90CRI, 3850 delivered lumens,
 120-277V, 0-10V dimming.



P350072-129-30



P350072-129-30

All fixtures:



Apogee LED

Tiered metal banded trim holds a half-circle etched glass shade.

P710036-009-30 Brushed Nickel
P710036-129-30 Architectural Bronze
15" W., 7-1/2" ht., Extends 3-11/16"
20w integrated LED, 3000K,
90CRI, 940 delivered lumens,
120-277V, 0-10V dimming.



P710036-009-30



P710036-129-30