

Sanford

FINISHES

- Brushed Nickel - 009
- Architectural Bronze - 129

Sanford

P2594-0930K Brushed Nickel

P2594-12930K Architectural Bronze

P2594-12930K

Sanford delivers ultra powerful air movement and energy efficient illumination packaged in a modern design. Ideal for both interior and outdoor settings, this "fandelier" adds a contemporary style to porches, foyers, bath and vanity areas providing a wide range of applications. Sanford includes an integrated 23W LED module, offering both form and function with energy and cost-savings benefits. A three-speed remote control is included.



P2594-0930K



P2594-12930K

Indoor or Outdoor Use

Contemporary Style



Powerful Air Movement

ENERGY INFORMATION AT HIGH SPEED

Airflow	1,008 cubic feet per minute
Electricity Use	37 watts (excludes lights)
DOE Weighted CFM/W	27 CFM/W

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- Metal blades
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

22-7/8" dia., 17-3/4" ht.
80" lead wires.

LAMP

23w LED Module, 3000K,
90 CRI, dimmable.



Three-Speed Remote Control Included
Three-speed fan operation
Full-range dimming for light

