

# Huff

P250030-009  
shown with Brushed Nickel blades

## FINISHES

- Brushed Nickel - 009
- Satin White- 028
- Black- 031

The hassles and headaches of the day fade away under the relaxing airflow created by the Huff Collection. Six expansive aluminum blades with decorative winglets stretch out from a dual mount center. Select a brushed nickel, matte white, or matte black finish all with their own complementary highlights to create a perfect design for your modern or transitional space.


*Complimentary Highlights*

*Modern Design*

*Expansive Aluminum Blades*


# Huff

**P250030-009** Brushed Nickel



Brushed Nickel

**P250030-028** Satin White



Satin White

**P250030-031** Black



Black



P250030-009  
shown with Brushed Nickel blades



P250030-028  
shown with Satin White blades



P250030-031  
shown with Black blades

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	14,482 cubic feet per minute
<b>Electricity Use</b>	49 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	344 CFM/W

## FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Aluminum blades
- Compatible with universal light kit
- Remote control with batteries is included

## SIZE

96" dia., 15-1/2" ht.  
80" lead wires.



Full Function Remote Control Included  
Six-speed fan operation  
Reverse direction control