

Vast

P2550-3130K
shown with Black blades

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- White - 30
- Black - 31

Beautiful and expansive in design, the 72" Vast ceiling fan is ideal for use in large areas and outdoor covered areas for maximum cooling. A white opal shade complements a variety of finish options, including Brushed Nickel with Chrome accents, Antique Bronze, White with Chrome accents or Matte Black. Vast features a dual mount system and comes with a full function remote control.




Vast

P2550-0930K Brushed Nickel



P2550-2030K Antique Bronze



P2550-3030K White



P2550-3130K Black



P2550-0930K
shown with Brushed Nickel blades
and Chrome accents



P2550-2030K
shown with Antique Bronze blades



P2550-3030K
shown with White blades
and Chrome accents



P2550-3130K
shown with Black blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	6,933 cubic feet per minute
Electricity Use	21 watts (excludes lights)
DOE Weighted CFN/W	322 CFM/W

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Aluminum blades
- White opal glass
- Remote control with batteries is included

SIZE

72" dia., 16-3/4" ht
80" lead wires.

LAMP

18w LED Module, 3000K, 90 CRI,
1400 lumens, dimmable.



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control

