

Fresnel Lens

Industrial roots in form and function. Antique-inspired Fresnel glass lens in Brushed Nickel, Oil Rubbed Bronze, or Chrome.

FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15
- Oil Rubbed Bronze - 108

ONE-LIGHT PENDANT

P5188-09 Brushed Nickel
P5188-108 Oil Rubbed Bronze
 12-1/8" dia., 10-1/2" ht.
 Overall ht. w/stem 77"; wire 10'.
 One medium base lamp,
 100w max.

LED PENDANT

P5188-0930K9 Brushed Nickel
P5188-1530K9 Polished Chrome
P5188-10830K9 Oil Rubbed Bronze
 12-1/8" dia., 10-1/2" ht.
 Overall ht. w/stem 77"; wire 10'.
 One 17w LED module, 3000K,
 90CRI, 1211 Source Lumens.



ONE-LIGHT PENDANT

P5197-09 Brushed Nickel
P5197-108 Oil Rubbed Bronze
 16" dia., 13-1/4" ht.
 Overall ht. w/stem 79"; wire 10'.
 One medium base lamp,
 100w max.

LED PENDANT

P5197-0930K9 Brushed Nickel
P5197-1530K9 Polished Chrome
P5197-10830K9 Oil Rubbed Bronze
 16" dia., 13-1/4" ht.
 Overall ht. w/stem 79"; wire 10'.
 One 17w LED module, 3000K,
 90CRI, 1211 source lumens.



Featuring Fresnel Lens
 Image: Keystone Custom Homes



MINI-PENDANT

P5050-09 Brushed Nickel
P5050-108 Oil Rubbed Bronze
 6-1/8" dia., 6-1/4" ht. Overall ht.
 w/stem 72-1/4"; wire 10'.
 One medium base lamp,
 40w max.

LED MINI-PENDANT

P5050-0930K9 Brushed Nickel
P5050-1530K9 Polished Chrome
P5050-10830K9 Oil Rubbed Bronze
 6-1/8" dia., 6-1/4" ht.
 Overall ht. w/stem 72-1/4"; wire 10'.
 One 9w LED module, 3000K, 90CRI,
 623 source lumens.



Fresnel LED



P350113-009-30



P350113-108-30



P350113-015-30

Industrial styling with a nautical-inspired Fresnel glass lens offers both form and function.

LED FLUSH MOUNT

P350113-009-30 Brushed Nickel

P350113-015-30 Polished Chrome

P350113-108-30 Oil Rubbed Bronze

12-3/4" dia., 4-1/2" ht.

One 17w LED module, 3000K, 90CRI, 1276 source lumens.

All fixtures:

