

Linen LED

White linen glass bowl trimmed with metal banding and punctuated with a metal knob.



P350005-009-30



P350006-009-30



P350007-009-30



P350008-009-30

LED FLUSH MOUNT

P350005-009-30 Brushed Nickel
11" dia., 4-5/8" ht.
21w integrated LED, 3000K,
90CRI, 921 delivered lumens.

LED FLUSH MOUNT

P350006-009-30 Brushed Nickel
13" dia., 5-3/8" ht.
21w integrated LED, 3000K,
90CRI, 1152 delivered lumens.

LED FLUSH MOUNT

P350007-009-30 Brushed Nickel
15" dia., 5-7/8" ht.
28w integrated LED, 3000K,
90CRI, 1389 delivered lumens.

LED FLUSH MOUNT

P350008-009-30 Brushed Nickel
19" dia., 7-1/8" ht.
30w integrated LED, 3000K,
90CRI, 1984 delivered lumens.

All fixtures:

