

Sconces LED

Sconces styles to suit any décor offer LED lamping for beauty plus energy efficiency.

P7083-0930K9 Brushed Nickel
White Acrylic
8-7/8" W., 10-5/8" ht.
Extends 4". H/CTR 5-3/8".
One 17w LED module, 3000K,
90 CRI, 1211 source lumens.



P7092-0930K9



P7083-0930K9

P7085-0930K9 Brushed Nickel
White Acrylic
9-1/2" W., 10-5/8" ht.
Extends 3-3/4". H/CTR 10-3/8".
One 17w LED module, 3000K,
90 CRI, 1211 source lumens.



P7085-0930K9



P7088-0930K9

P7088-0930K9 Brushed Nickel
White Acrylic
8" W., 10-5/8" ht.
Extends 3-7/8". H/CTR 5-3/8".
One 17w LED module, 3000K,
90 CRI, 1211 source lumens.

P7092-0930K9 Brushed Nickel
Etched Opal Enclosed
One-piece Glass
8" W., 10-3/4" ht.
Extends 4". H/CTR 5-1/2".
One 17w LED module, 3000K,
90 CRI, 1211 source lumens.



P7093-3030K9
Shown with Brushed Nickel finial



P7093-3030K9
Shown with Bronze finial

P7093-3030K9 Brushed Nickel
Satin Opal Glass
11-3/8" W., 11-1/8" ht.
Extends 3-3/8". H/CTR 5-5/8".
One 17w LED module, 3000K,
90 CRI, 1211 source lumens.

P7105-0930K9 Brushed Nickel
Ribbed Glass
12-7/8" W., 10" ht.
Extends 3-1/2". H/CTR 6-3/8".
One 17w LED module, 3000K,
90 CRI, 1211 source lumens.



P7105-0930K9

All fixtures:



Sconces LED

Sconces styles to suit any décor offer LED lamping for beauty plus energy efficiency.

P710010-009-30 BRUSHED NICKEL
P710010-129-30 ARCHITECTURAL BRONZE
6-3/4" W., 12" ht. Extends 4". H/CTR 6".
One 9w LED module, 3000K
90CRI, 624 source lumens.



P710010-009-30



P710010-129-30