


Outdoor Transformers

Magnetic Low Voltage — Plug-In Compatible

- Multiple secondary taps of 12, 13 and 15 volts allow maximum light output and lamp life for long or short runs and loading variations (300, 600 and 900 watt units only).
- Three foot 12 gauge cord with grounding plug.
- Thermal protection in the primary circuit to avoid overheating.
- Resettable circuit breakers in secondary circuits for electrical safety and convenience.
- Weatherproof construction, powder-coat painted (P8522-31 and P8523-31).
- Stainless steel construction (P8519-01, P8520-01 and P8521-01).
- Easy open enclosure with KO's for hardwiring and photocell installation.
- Easy wire terminal board for secondary connections.
- For outdoor use.
- Plug in timer and photocell compatible, see below.



PRODUCT	WATT	DESCRIPTION	SIZE (W X H X D)
P8519-01	300	300w stainless steel	5-3/8" x 17" x 5-3/8"
P8520-01	600	(2) 300w circuits, stainless steel	6-5/8" x 17" x 5-5/8"
P8521-01	900	(3) 300w circuits, stainless steel	6-5/8" x 19" x 5-1/2"
P8522-31	300	300w	5-1/4" x 17" x 5-5/8"
P8523-31	600	(2) 300w circuits	6-1/2" x 17" x 5-5/8"

*All fixtures:
The above magnetic low voltage transformers are suitable for providing 12V power to both 12V low voltage incandescent fixtures and 12V low voltage LED fixtures.*

Magnetic Transformer Accessories

P8524-01 Two-prong plug-in timer
2-3/4" W., 3-1/8" ht.
Allows multiple settings.



P8525-31 Direct mount photo-cell.
1-5/8" dia., 4-7/8" length.
Turns transformer on at dusk and off when ambient light appears.



P8531-01 Digital timer
3"w, 4-1/8" ht, extends 1-5/8"
Allows multiple settings.



P8526-31 Remote mount photo-cell.
1-3/8" dia., 5-1/4" length
Turns on transformer at dusk and off when ambient light appears.
Includes 10 ft. of cord.



Outdoor Transformers

LED Low Voltage Transformer

P8270-31 Non metallic case protects timer controls and 120v to 12v transformer. Surge protected with grounded cord/plug set and easy 12V cable attachment. Photocontrol triggers "time on", eliminating seasonal adjustment. 56w max. Non-dimmable. Recommend using 14 gauge cable.



PRODUCT	WATT	DESCRIPTION	SIZE (W X H X D)
P8270-31	56	45w LED	4" x 5-5/8" x 3-1/2"

The above electronic 12V LED low voltage transformer is designed to operate 12V low voltage LED fixtures only. It cannot operate low voltage incandescent or halogen fixtures.

Electronic Low Voltage

P8517-31 supplied with integral photo-cell. Non-metallic housing to prevent corrosion. Three foot 18-gauge cord with grounding plug. Suitable for outdoor installation only. 20w minimum.



P8518-31 supplied with remote mount photo-cell with auto setting and 2 hr., 6 hr., and 8 hr. shut off settings. Suitable for outdoor installation only. 20w minimum.



PRODUCT	WATT	DESCRIPTION	SIZE (W X H X D)
P8517-31	150	150w electronic	3-5/8" x 6-1/2" x 2-3/8"
P8518-31	300	300w electronic	5-1/8" x 7-1/4" x 2-3/4"

*All fixtures:
The above electronic low voltage transformers are suitable for providing 12V power to both 12V low voltage incandescent fixtures and 12V low voltage LED fixtures.*