

Line Voltage



P5204-38



P5204-31



P5235-31



P5205-31



P5313-31



P5205-31

shown with P5313-31 pole

PAGODA

P5204-38 Green

P5204-31 Black

Die-cast aluminum. Clear glass liner.

½ NPS threaded fitting for

permanent or P5233 for

portable installation.

Cannot be used with P5312-31.

6" dia., 7-1/8" ht.

One medium base lamp,

100w max.

BOLLARD

P5205-31 Black

Etched glass.

½ NPS threaded fitting for

permanent or P5233 installation.

For Bollard mount order with

P5313-31 pole or P8562-31.

5" dia., 6-1/4" ht.

One medium base lamp,

60w max.

FLOOD LIGHT

P5235-31 Black*

Black powder-coat painted

aluminum resists chipping and

fading. Clear lens. Locking

vertical adjustment.

5-1/4" dia., 8-1/4" long.

One PAR 38, 150w max.

BOLLARD AND POLE

P5313-31 Black

Bollard Pole for P5205-31.

(order each separately).

4-3/4" dia., 28-3/8" ht.

Accepts P5205-31 only.

BOLLARD POLE MOUNT

Mount P5205-31 on top of bollard

to spread wider circles of light and

to coordinate ground lights with

bollards. Aluminum construction

with pedestal and "J" bolts for

surface mounting on paved areas

or atop walls. For complete unit

order bollard accessory and light.