

Rushton

FINISH

- Brushed Nickel - 009
- Graphite - 143

P300228-143

Celebrate the past with the industrial-styled Rushton vanity. Mechanical details like a pulley wheel complete with a faux cord holding a clear glass shade, an antique style socket, and an exposed bulb (not included) add vintage charm. The mixed metal fixture is offered in either Brushed Nickel accented with a Black tube arm, or Graphite with an Antique Brass tube arm, for a look that preserves a sense of history.

Mechanical Detail

Mixed Metals



Antique Style Socket

ONE-LIGHT BATH

P300226-143 Graphite
5" W., 9-1/2" ht.,
Extends 6". H/CTR 6-1/2".
One medium base lamp,
60w max.



P300226-143

TWO-LIGHT BATH

P300227-143 Graphite
16" W., 9-1/2" ht.,
Extends 6". H/CTR 7".
Two medium base lamps,
each 60w max.



P300227-143

THREE-LIGHT BATH

P300228-143 Graphite
24" W., 9-1/2" ht.,
Extends 6". H/CTR 7".
Three medium base lamps,
each 60w max.



P300228-143

FOUR-LIGHT BATH

P300229-143 Graphite
32" W., 9-1/2" ht.,
Extends 6". H/CTR 7".
Four medium base lamps,
each 60w max.



P300229-143



P300226-009



P300227-009



P300228-009



P300229-009

ONE-LIGHT BATH

P300226-009 Brushed Nickel
5" W., 9-1/2" ht.,
Extends 6". H/CTR 6-1/2".
One medium base lamp,
60w max.

TWO-LIGHT BATH

P300227-009 Brushed Nickel
16" W., 9-1/2" ht.,
Extends 6". H/CTR 7".
Two medium base lamps,
each 60w max.

THREE-LIGHT BATH

P300228-009 Brushed Nickel
24" W., 9-1/2" ht.,
Extends 6". H/CTR 7".
Three medium base lamps,
each 60w max.

FOUR-LIGHT BATH

P300229-009 Brushed Nickel
32" W., 9-1/2" ht.,
Extends 6". H/CTR 7".
Four medium base lamps,
each 60w max.

*All fixtures shown with P7825-01
vintage lamps, not included.*

Featuring Rushton

