

Archie

The Archie Collection features finely crafted strap and knob details with clear, double-prismatic glass shades. Smooth stems and backplates support each shade and are coated in a crisp polished chrome, handsome Venetian bronze, or understated antique nickel finish.

FINISH

- Polished Chrome - 15
- Venetian Bronze - 74
- Antique Nickel - 81

ALSO IN

Bath
Close-to-Ceiling

PAIR WITH

Academy
Archives

WALL BRACKET

P2989-15 Polished Chrome

P2989-74 Venetian Bronze

P2989-81 Antique Nickel

5-3/4" W., 8-1/4" ht.,
Extends 7". H/CTR 5-1/4".

One medium base lamp,
100w max.

TWO-LIGHT LINEAR CHANDELIER

P4624-15 Polished Chrome

P4624-74 Venetian Bronze

30" W., 10-5/8" D., 12-3/4" ht.,
Overall ht. w/chain 100"; wire 10'.

Two medium base lamps,
each 100w max.

ONE-LIGHT PENDANT

P5026-15 Polished Chrome

P5026-74 Venetian Bronze

P5026-81 Antique Nickel

10-1/2" W., 9-1/4" ht.,

Overall ht. w/stem 75"; wire 10'.

One medium base lamp,
each 100w max.

MINI PENDANT

P5173-15 Polished Chrome


P5173-74 Venetian Bronze

P5173-81 Antique Nickel

5-3/4" W., 8-3/4" ht.,

Overall ht. w/stem 75"; wire 10'.

One medium base lamp,
each 100w max.



Archie

FINISHES

- Polished Chrome - 15
- Antique Nickel - 81
- Venetian Bronze - 74
- Vintage Brass - 163

ALSO IN

- Pendants
- Close-to-Ceiling

P2992-81

A welcomed blast from the past returning to a design grounded in aesthetic authenticity. Finely crafted strap and knob details with clear double prismatic glass.

Double Prismatic Glass



Knob Details

Aesthetic Authenticity

ONE-LIGHT BATH

P2989-81 Antique Nickel
5-3/4" W., 8-1/4" ht.
Extends 7". H/CTR 5-1/4".
One medium base lamp,
100w max.



P2989-81

TWO-LIGHT BATH

P2991-81 Antique Nickel
17" W., 8-3/4" ht.
Extends 7". H/CTR 5-1/4".
Two medium base lamps,
each 100w max.



P2991-81

THREE-LIGHT BATH

P2992-81 Antique Nickel
26-1/4" W., 8-3/4" ht.
Extends 7". H/CTR 5-1/4".
Three medium base lamps,
each 100w max.



P2992-81

FOUR-LIGHT BATH

P2997-81 Antique Nickel
35-1/2" W., 8-3/4" ht.
Extends 7". H/CTR 5-1/4".
Four medium base lamps,
each 100w max.



P2997-81

All fixtures mount up or down.

Archie

ONE-LIGHT BATH

P2989-15 Polished Chrome
P2989-74 Venetian Bronze
P2989-163 Vintage Brass
5-3/4" W., 8-1/4" ht.
Extends 7". H/CTR 5-1/4".
One medium base lamp,
100w max.



P2997-163

P2989-163

TWO-LIGHT BATH

P2991-15 Polished Chrome
P2991-74 Venetian Bronze
P2991-163 Vintage Brass
17" W., 8-3/4" ht.
Extends 7". H/CTR 5-1/4".
Two medium base lamps,
each 100w max.



P2992-163

P2991-163

THREE-LIGHT BATH

P2992-15 Polished Chrome
P2992-74 Venetian Bronze
P2992-163 Vintage Brass
26-1/4" W., 8-3/4" ht.
Extends 7". H/CTR 5-1/4".
Three medium base lamps,
each 100w max.



P2997-74

P2989-74

FOUR-LIGHT BATH

P2997-15 Polished Chrome
P2997-74 Venetian Bronze
P2997-163 Vintage Brass
35-1/2" W., 8-3/4" ht.
Extends 7". H/CTR 5-1/4".
Four medium base lamps,
each 100w max.



P2992-74

P2991-74

All fixtures mount up or down.



P2997-15

P2989-15



P2992-15

P2991-15

Archie

A cross-patterned, double-prismatic glass shade is grounded by a metal frame and knob.

SEMI-FLUSH CONVERTIBLE

P2334-15 Polished Chrome

P2334-74 Venetian Bronze

P2334-81 Antique Nickel

P2334-163 Vintage Brass

Hanging and ceiling mount hardware included.

12-3/8" dia., 11-3/8" ht.,

Overall ht. w/chain 48-1/2"; wire 10'.

Two medium base lamps, each 100w max.

TWO-LIGHT FLUSH MOUNT

P3740-15 Polished Chrome

P3740-74 Venetian Bronze

P3740-81 Antique Nickel

P3740-163 Vintage Brass

12-3/8" dia., 6-1/4" ht.

Two medium base lamps, each 75w max.



P2334-81



P2334-74



P2334-15



P2334-163



P3740-81



P3740-74



P3740-15



P3740-163