

Applause



P4037-09



P5010-09

FINISH

- Brushed Nickel - 09
- Antique Bronze - 20

ALSO IN

Bath
Close-to-Ceiling

PAIR WITH

Trinity
Classic

WALL BRACKET

P2095-09 Brushed Nickel
P2095-20 Antique Bronze
7" W., 9-1/8" ht.,
Extends 7-7/8". H/CTR 5-3/4".
One medium base lamp,
100w max.



P2095-09

FIVE-LIGHT CHANDELIER

P4036-09 Brushed Nickel
P4036-20 Antique Bronze
24-1/2" dia., 24-5/8" ht.,
Overall ht. w/chain 99"; wire 15'.
Five medium base lamps,
each 100w max.



P4036-09



P4036-20

NINE-LIGHT CHANDELIER

P4037-09 Brushed Nickel
P4037-20 Antique Bronze
29-1/4" dia., 31-3/4" ht.,
Overall ht. w/chain 145-1/2"; wire 15'.
Nine medium base lamps,
each 100w max.



P4037-20



P5010-20

MINI-PENDANT

P5010-09 Brushed Nickel
P5010-20 Antique Bronze
7" dia., 6-1/2" ht.,
Overall ht. w/stem 72-1/2"; wire 10'.
One medium base lamp,
100w max.



P2095-20

Applause

Applause is comprised of etched natural parchment glass paired with a classic iron form with Antique Bronze finish and etched parchment glass with Brushed Nickel finish.

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

ALSO IN

Collections
Close-to-Ceiling

ONE-LIGHT BATH

P2095-09 Brushed Nickel

P2095-20 Antique Bronze

7" W., 9-1/8" ht.

Extends 7-7/8". H/CTR 5-3/4".

One medium base lamp,
100w max.



P2095-09



P2096-09



P2097-09



P2105-09

TWO-LIGHT BATH

P2096-09 Brushed Nickel

P2096-20 Antique Bronze

16-1/4" W., 8-1/2" ht.

Extends 9". H/CTR 6".

Two medium base lamps,
each 100w max.

THREE-LIGHT BATH

P2097-09 Brushed Nickel

P2097-20 Antique Bronze

24" W., 8-1/2" ht.

Extends 9". H/CTR 6".

Three medium base lamps,
each 100w max.



P2095-20



P2096-20

FOUR-LIGHT BATH

P2105-09 Brushed Nickel

P2105-20 Antique Bronze

34" W., 8-1/2" ht.

Extends 9". H/CTR 6".

Four medium base lamps,
each 100w max.



P2097-20



P2105-20

All fixtures mount up or down.

Applause

Traditional iron forms hold natural parchment-patterned or etched white parchment glass shades.

TWO-LIGHT FLUSH MOUNT

P3617-09 Brushed Nickel

P3617-20 Antique Bronze
14" dia., 9" ht.

Two medium base lamps,
each 60w max.



P3617-20



P3617-09