

# Emblem Eyeball Recessed Trims LED

The Emblem Eyeball LED recessed trim is ideal for use in both new construction as well as remodel/retrofit installations. Adjustable light source is great for directing the light at walls and items you want to accent. Offered in 4", 5" and 6" sizes and 4 finishes to match interior décor. The deep trim offers 360° positioning and 30° tilt to adjust the beam direction.

## TRIM FEATURES

- The trim is equipped with both Edison base adapter and quick link connector allowing easy installation in many standard medium based socket recessed housings and Progress LED recessed housings.
- A polycarbonate diffused lens reduces glare and pixilation from LEDs.
- Trim uses friction springs for easy installation into recessed housings.
- cCSAus Listed for Damp Locations, Energy Star.
- Flicker free dimming down to 10% with many Triac or ELV dimmers.
- Suitable for use in IC and Non IC applications.
- LEDs are 3000K, CRI 90+ and rated for 50,000 hours.

## 4" Eyeball Trim

**P8046-09-30K** Brushed Nickel  
**P8046-20-30K** Antique Bronze  
**P8046-28-30K** White  
**P8046-31-30K** Black  
Integrated LED, 630 lumens,  
66 lumens per watt, equivalent to 50W  
R20 incandescent lamp.



P8046-09-30K



P8046-20-30K



P8046-28-30K



P8046-31-30K

## COMPATIBLE RECESSED HOUSINGS

P830-LED  
P831-LED  
P832-LED  
P830-TG  
P831-AT  
P832-TG

## 5" Eyeball Trim

**P8176-09-30K** Brushed Nickel  
**P8176-20-30K** Antique Bronze  
**P8176-28-30K** White  
**P8176-31-30K** Black  
Integrated LED, 670 lumens,  
63 lumens per watt, equivalent  
to 65W BR30 incandescent lamp.



P8176-09-30K



P8176-20-30K



P8176-28-30K



P8176-31-30K

## COMPATIBLE RECESSED HOUSINGS

P84-LED  
P851-ICAT  
P1841-LED  
P1851-ICAT  
P1841-ICAT

## 6" Eyeball Trim

**P8076-09-30K** Brushed Nickel  
**P8076-20-30K** Antique Bronze  
**P8076-28-30K** White  
**P8076-31-30K** Black  
Integrated LED, 700 lumens,  
66 lumens per watt, equivalent  
to 65W BR30 incandescent lamp.



P8076-09-30K



P8076-20-30K



P8076-28-30K



P8076-31-30K

## COMPATIBLE RECESSED HOUSINGS

P87-AT  
P87-ATQC  
P87-LED  
P187-TG

All fixtures:

