

8" Recessed

Sloped Ceiling Housings

For complete fixture, order housing with trim.



New Construction Air-Tight & IC with E26 socket

P45-AT

Ceiling opening: 8-3/4"
Plaster frame: 15-3/4" x 9-3/4"
Recessed depth: 7-1/2"
Pryouts: 1/2" and 3/4"

P45-AT HOUSING FEATURES

- Maintains lamp in a vertical position in 9° to 45° ceilings (2/12 to 12/12 pitch).
- UL & CUL listed for damp locations and through wiring.
- Meets Washington State Energy Code requirements.
- Can be installed in ceilings from 1/2" to 1-1/2" thick.
- Integral nailer and T-bar mounting clamp.
- Single spring installation of trims.



Remodel IC with E26 socket

P245-TG

Ceiling opening: 8"
Recessed depth: 7-13/16"
Pryouts: 1/2"

P245-TG HOUSING FEATURES

- Cast trim flange is integral part of housing.
- UL and CUL listed for damp locations and through wiring.
- Can be installed in ceilings from 1/2" to 1-1/2" thickness.
- Lamp is adjustable to vertical position in 9° to 45° ceilings (2/12 to 12/12 pitch).
- Exclusive mounting bars permit quick and solid mounting.
- Rated for 4 #12 90° conductors (2 in/2 out).
- Rated for 60° supply wires in end of run applications.
- Single spring installation of trims.

Trims

9-3/4" outside diameter.



BAFFLE

P8000-28 White
P45-AT 120w PAR38, BR40
P245-TG 75w PAR38, BR40



BAFFLE

P8000-31 Black
P45-AT 120w PAR38, BR40
P245-TG 75w PAR38, BR40



ALZAK® CONES

P8001-21 Clear Alzak®
P45-AT 120w PAR38, BR40
P245-TG 75w PAR38, BR40

Lamp wattages shown are maximum.
For accessories see page 795.