

Linear Undercabinet LED

HIDE a LITE™

The HIDE-a-LITE™ Linear undercabinet series provides the ideal solution for residential and light commercial applications. The luminaire is constructed from an aluminum housing and features a lens designed to optimize light distribution, ensuring for proper illumination of the work space below. The HIDE-A-LITE linear undercabinet utilizes a through hole mounting method to allow for an easy installation. The luminaire can be direct wired, removing the need for separate cords. Two armored cable fittings are included with the product for applications requiring the use of armored cable. An on/off switch is located on the front of the luminaire, allowing for easy access when used as a task light. The energy efficient LEDs can be dimmed down to 10% with many forward phase (TRIAC) and electronic low voltage (ELV) dimmers.

9" LED UNDERCABINET

P700000-020-30 Antique Bronze

P700000-028-30 White

9" L., 3-1/4" W., 1-1/8" ht.

One 4.5w integrated LED, 3000K, 90CRI, 300 delivered lumens.



P700000-028-30



P700000-020-30

12" LED UNDERCABINET

P700001-020-30 Antique Bronze

P700001-028-30 White

11-1/2" L., 3-1/4" W., 1-1/8" ht.

One 7.5w integrated LED, 3000K, 90CRI, 500 delivered lumens.



P700001-028-30



P700001-020-30

18" LED UNDERCABINET

P700002-020-30 Antique Bronze

P700002-028-30 White

17-1/2" L., 3-1/4" W., 1-1/8" ht.

One 12.5w integrated LED, 3000K, 90CRI, 815 delivered lumens.



P700002-028-30



P700002-020-30

24" LED UNDERCABINET

P700003-020-30 Antique Bronze

P700003-028-30 White

23-1/2" L., 3-1/4" W., 1-1/8" ht.

One 15.5w integrated LED, 3000K, 90CRI, 980 delivered lumens.



P700003-028-30



P700003-020-30

36" LED UNDERCABINET

P700004-020-30 Antique Bronze

P700004-028-30 White

35-1/2" L., 3-1/4" W., 1-1/8" ht.

One 20w integrated LED, 3000K, 90CRI, 1500 delivered lumens.



P700004-028-30



P700004-020-30

All fixtures:

