

Emblem Surface Mount LED

Easy installation and a sleek, modern lighting aesthetic are offered by our Emblem Surface Mount LED Collection. An excellent choice for general ambient lighting, each polished design features a smooth, slightly tapered trim ring surrounding a single, integrated LED light source. Enjoy the unmatched level of glare control offered by the fixture's diffused polycarbonate lens that also hides any unwanted LED pixelation. Each light fixture is home to an integrated AC LED light engine that seamlessly installs to a variety of ceiling pan junction boxes to give you added flexibility when it comes to creating your design vision. The surface mount provides unparalleled longevity with its, 50,000-hour LED life span and 80% energy savings.

LED FEATURES

- Wet location listed.
- 120v input voltage.
- 60 Lumens per watt.
- Flicker-free dimming with many Triac and ELV dimmers.
- 50,000 hour life.

P810014-020-30 Antique Bronze

P810014-028-30 Satin White

7-1/4" dia., 1-3/8" ht.

15.5w integrated LED,

3000K, 90CRI, 1080 lumens.



P810014-028-30



P810014-020-30K

P810027-020-30 Antique Bronze

P810027-028-30 Satin White

5-1/2" dia., 1-7/8" ht.

12.5w integrated LED,

3000K, 90CRI, 750 lumens.



P810027-028-30



P810027-020-30K



Shown installed into
1/2" ceiling pan J-box

All fixtures:



JAB