


# Lamp Reference Chart


## Medium Base - E26



## Candelabra Base - E12



## PIN Base



## Equivalent Light Output

The following wattages are now available for medium base A lamps. It is at our customers discretion to install CFL or LED bulbs. Pay careful attention to the bulb manufacturer's caution statements regarding use in enclosed fixtures or dimmer compatibility.

LEGACY BULBS WATTS (W)	EISA COMPLIANT INCANDESCENT BULBS (W)	TYPICAL LIGHT OUTPUT (LUMENS)	COMMON CFL LIGHT BULBS WATTS (W)	TYPICAL LED LIGHT BULBS WATTS (W)
40	29	450	9-13	5
60	43	800	13-15	9
75	53	1,100	18-25	13
100	72	1,600	23-30	17
150	N/A	2,600	30-52	22

# Lamps

## Vintage Lamps



**P7825-01**  
Overall L. 5-7/16" maximum.  
40w ST64 Edison E26  
medium base. Vintage  
Amber bulb.



**P7827-01**  
Overall L. 5-7/16" maximum.  
40w T9 E26 medium base.  
Vintage Amber bulb.



**P7826-01**  
Overall L. 3-1/2" maximum.  
40w T8 E12 candelabra base.  
Vintage Amber bulb.

## LED Lamps



**LED LAMP**  
**F8.5A19DLED927/JA8**  
8.5W A19 LED medium base  
filament lamp.  
2700K, 600 lumens,  
1500 hours, dimmable.



**LED LAMP**  
**F4B10DLED927/JA8**  
4W B10 LED candelabra  
base filament lamp.  
2700K, 300 lumens,  
1500 hours, dimmable.



**LED LAMP**  
**F4T10DLED927/JA8**  
4w T10 LED medium base  
filament lamp  
2700K, 300 lumens,  
15,000 hours, dimmable.



**VINTAGE LED LAMP**  
**V6.5ST19DLED922/JA8**  
6.5w ST19 LED medium base  
amber filament lamp  
2200K, 450 lumens,  
15,000 hours, dimmable.



**LED LAMP**  
**3G9DLED27**  
3w LED G9 base lamp  
2700K, 270 lumens,  
25,000 hours, dimmable.



**LED LAMP**  
**EF4T8D927/JA8**  
4w T8 LED candelabra  
base filament lamp  
2700K, 300 lumens,  
15,000 hours, dimmable.



**LED LAMP**  
**EF6.5T10DL9927/JA8**  
6.5w T10 LED medium  
base filament lamp  
2700K, 600 lumens,  
15,000 hours, dimmable.



**LED LAMP**  
**F7ST19DLED927/JA8**  
7w ST19 LED medium base  
filament lamp  
2700K, 600 lumens,  
15,000 hours, dimmable.



## Landscape Lamps



**P7801-01**  
18w T5 wedge base  
clear lamp, 12v.



**P7812-01**  
35w G9 halogen  
frosted lamp, 120v.



**P7818-01**  
6-pack of 60w G9 halogen  
frosted lamps, 120v.

## Krypton Lamps



**P7807-01**  
E12 (candelabra)  
frosted lamp, 120v.