

Bedford



P4391-09

FINISH

● Brushed Nickel - 09

PAIR WITH

Americana
Drum Shade

SEMI-FLUSH CONVERTIBLE

P3788-09 Brushed Nickel
Hanging and ceiling mount
hardware included.
10-1/2" dia., 14-1/2" ht.,
Overall ht. w/chain 54"; wire 15'.
One medium base lamp,
150w max.

THREE-LIGHT CHANDELIER

P4390-09 Brushed Nickel
19-1/2" dia., 15-5/8" ht.,
Overall ht. w/chain 54"; wire 15'.
Three medium base lamps,
each 100w max.



P4390-09

FIVE-LIGHT CHANDELIER

P4391-09 Brushed Nickel
22-1/2" dia., 16" ht.,
Overall ht. w/chain 91"; wire 15'.
Five medium base lamps,
each 100w max.

ONE-LIGHT PENDANT

P5090-09 Brushed Nickel
15-5/8" dia., 11-1/4" ht.,
Overall ht. w/chain 50"; wire 15'.
One medium base lamp,
150w max.



P3788-09



P5090-09

Bedford

Brushed Nickel finish highlights curved double arms and etched alabaster glass.

FINISH

● Brushed Nickel - 09

ALSO IN

Collections



P3368-09

TWO-LIGHT BATH

P3368-09 Brushed Nickel
14-3/8" W., 8-3/8" ht.
Extends 6-1/4". H/CTR 3-1/8".
Two medium base lamps,
each 100w max.



P3369-09

THREE-LIGHT BATH

P3369-09 Brushed Nickel
16-1/4" W., 8-1/4" ht.
Extends 9-1/2". H/CTR 3-1/8".
Three medium base lamps,
each 100w max.

Bedford

Softly diffused alabaster glass shades on a finely crafted metallic frame.

SEMI-FLUSH CONVERTIBLE

P3788-09 Brushed Nickel
Hanging and ceiling mount hardware included.
10-1/2" dia., 14-1/2" ht.,
Overall ht. w/chain 54"; wire 15'.
One medium base lamp,
150w max.



P3788-09