

New Haven

A Black finish complements clear beveled glass in the New Haven outdoor lantern collection.

FINISH

- Black - 31

POST LANTERN

P6433-31 Black
11" dia., 23" ht.
Fits 3" post (sold separately).
Three candelabra base lamps,
each 60w max.

HANGING LANTERN

P6533-31 Black
11" dia., 19-3/4" ht.
Overall ht. w/chain 95"; wire 10'.
Three candelabra base lamps,
each 60w max.

FLUSH MOUNT

P550036-031 Black
11" dia., 6" ht.
Two medium base lamps,
each 60w max.

SMALL WALL LANTERN

P6610-31 Black
7-5/8" W., 14-7/8" ht.
Extends 7-3/8". H/CTR 5-1/2".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P6611-31 Black
9" W., 18-1/8" ht.
Extends 8-5/8". H/CTR 8-1/2".
One candelabra base lamp,
100w max.

LARGE WALL LANTERN

P6612-31 Black
11" W., 21-7/8" ht.
Extends 10-3/8". H/CTR 8-5/8".
Three candelabra base lamps,
each 60w max.



P550036-031

P6611-31



P6433-31

P6612-31