


Aluminum Squares

Heavy-duty aluminum construction, die-cast aluminum wall bracket. Listed for wet locations. Powder coat for chipping and fading resistance. Dark Sky compliant for down light only.

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P5643-20	Bronze	One-light 6" square 	6" W., 12" ht.	1 250w PAR-38 or 150w BR-40
P5643-30	White		Extends 8-7/8".	
P5643-31	Black		H/CTR 4-1/2".	
P5644-20	Bronze	Two-light 6" up/down square*	6" W., 18" ht.	2 250w PAR-38 or 150w BR-40
P5644-30	White		Extends 8-7/8".	
P5644-31	Black		H/CTR 8".	

*For use in wet locations, requires top cover lens, P860047.



P5643-20



P5643-30



P5643-31



P5644-20




P5644-30



P5644-31

Aluminum Squares LED

Heavy-duty aluminum construction, die-cast aluminum wall bracket. UL listed for wet locations. Powder coat for chipping and fading resistance. Dark Sky compliant for down light only. 3000K, 90+ CRI.

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P5643-2030K	Bronze	One-light 6" square LED 	6" W., 12" ht.	1 29w integrated LED 3000K, 90CRI, 1800 delivered lumens
P5643-3030K	White		Extends 8-7/8".	
P5643-3130K	Black		H/CTR 4-1/2".	
P5643-8230K	Metallic Gray			
P5644-2030K	Bronze	Two-light 6" LED up/down square*	6" W., 18" ht.	2 29w integrated LED 3000K, 90CRI, 1800 delivered lumens
P5644-3030K	White		Extends 8-7/8".	
P5644-3130K	Black		H/CTR 8".	
P5644-8230K	Metallic Gray			

*For use in wet locations, requires top cover lens, P860047.



P5644-2030K



P5644-3030K



P5643-2030K



P5643-3030K



P5643-3130K



P5643-8230K



P5644-3130K



P5644-8230K