

Polycarbonate Bulkheads



P5706-30



P5704-30



P5705-30



P5702-30



P5703-30

Virtually maintenance free fixtures. Install on ceilings or walls. Classic white details and trim, Corrosion, impact and shatter resistant, UV stabilized.

ROUND WALL OR CEILING

P5702-30 White

10" dia.,
Extends 4-3/4".
One medium base lamp,
75w max.

ROUND WALL OR CEILING

P5703-30 White

With grill.
10-3/8" dia.,
Extends 5-7/8".
One medium base lamp,
75w max.

OVAL WALL

P5704-30 White

10-1/2" L., 5-5/8" W.
Extends 3-3/4".
One medium base lamp,
60w max.



OVAL WALL

P5705-30 White

With grill.
10-1/2" L., 5-7/8" W.
Extends 4".
One medium base lamp,
60w max.



OVAL WALL

P5706-30 White

Hooded.
10-1/2" L., 5-7/8" W.
Extends 4-1/8".
One medium base lamp,
60w max.