

# Barlowe

## FINISHES

- Antique Bronze - 020
- Stainless Steel - 135

P550068-135

Metal Finishes

Farmhouse  
Style



Rustic X-Brace

Transform your home into a warm and cozy dream with the farmhouse-style of the Barlowe collection. A rustic X-brace design decorates each side of the charming lantern silhouettes. Metal finishes with antique copper or white accents provide added warmth and character.



P560156-135



P550068-135



P560157-135



P540068-135

**POST LANTERN**  
**P540068-135** Stainless Steel  
Fits 3" post (sold separately)  
9" sq., 20" ht.  
One medium base lamp,  
100w max.

**MEDIUM WALL LANTERN**  
**P560157-135** Stainless Steel  
7-1/2" W., 16" ht.  
Extends 8-1/2". H/CTR 3-1/2".  
One medium base lamp,  
100w max.

**HANGING LANTERN**  
**P550068-135** Stainless Steel  
9" sq., 21" ht.  
Overall ht. w/chain 96", wire 10'.  
One medium base lamp,  
100w max.

**LARGE WALL LANTERN**  
**P560158-135** Stainless Steel  
9-1/8" W., 19" ht.  
Extends 10". H/CTR 3-1/2".  
One medium base lamp,  
100w max.

**SMALL WALL LANTERN**  
**P560156-135** Stainless Steel  
6-1/2" W., 13" ht.  
Extends 7-1/2". H/CTR 2-3/8".  
One medium base lamp,  
100w max.



P560158-135



P550068-020



P560156-020



P560157-020



P540068-020



P560158-020

# Barlowe

## POST LANTERN

**P540068-020** Antique Bronze  
Fits 3" post (sold separately)  
9" sq., 20" ht.  
One medium base lamp,  
100w max.

## HANGING LANTERN

**P550068-020** Antique Bronze  
9" sq., 21" ht.  
Overall ht. w/chain 96", wire 10'.  
One medium base lamp,  
100w max.

## SMALL WALL LANTERN

**P560156-020** Antique Bronze  
6-1/2" W., 13" ht.  
Extends 7-1/2". H/CTR 2-3/8".  
One medium base lamp,  
100w max.

## MEDIUM WALL LANTERN

**P560157-020** Antique Bronze  
7-1/2" W., 16" ht.  
Extends 8-1/2". H/CTR 3-1/2".  
One medium base lamp,  
100w max.

## LARGE WALL LANTERN

**P560158-020** Antique Bronze  
9-1/8" W., 19" ht.  
Extends 10". H/CTR 3-1/2".  
One medium base lamp,  
100w max.

All fixtures shown with  
F7ST19DLED927/JA8 vintage lamps,  
not included.