

Crawford

P5574-108



Cast Lantern

Beveled Glass

Hinged Door

- FINISHES**
- Black - 31
 - Oil Rubbed Bronze - 108

The Crawford Collection offers updated traditional styling with scroll arms. Clear beveled or etched glass panes give off a soft glow of light while a hinged door makes maintenance easy and stress-free. This collection is ideal for illuminating new traditional and transitional settings.



P5671-108



P5574-108



P5672-108



P5670-108



P5673-108



P5474-108



P5686-108MD



P5686-31MD



P6630-31MD



P6631-31MD



P6632-31MD



P6633-31MD

Crawford

MEDIUM WALL LANTERN

P5686-31MD Black
P5686-108MD Oil Rubbed Bronze
 8-1/2" W., 16-3/4" ht.
 Extends 11". H/CTR 9-5/8".
 One medium base lamp,
 100w max.

SMALL WALL LANTERN

P6630-31MD Black
 6-1/2" W., 12-1/2" ht.
 Extends 8-3/4". H/CTR 8".
 One medium base lamp,
 100w max.

MEDIUM WALL LANTERN*

P6631-31MD Black
 8-1/2" W., 20-1/2" ht.
 Extends 11". H/CTR 8-3/8".
 One medium base lamp,
 100w max.

LARGE WALL LANTERN*

P6632-31MD Black
 9-7/8" W., 28-7/8" ht.
 Extends 12-5/8". H/CTR 11-5/8".
 One medium base lamp,
 100w max.

EXTRA LARGE WALL LANTERN*

P6633-31MD Black
 12" W., 32-7/8" ht.
 Extends 14-3/4". H/CTR 14-7/8".
 One medium base lamp,
 100w max.

**Hinged door for easy relamping.*

POST LANTERN*
P5474-108 Oil Rubbed Bronze
 12" dia., 28-1/2" ht.
 Fits 3" post (sold separately).
 Four candelabra base lamps,
 each 60w max.

MEDIUM WALL LANTERN*
P5671-108 Oil Rubbed Bronze
 8-1/2" W., 16-3/4" ht.
 Extends 11-1/8" H/CTR 9-5/8".
 Two candelabra base lamps,
 each 60w max.

HANGING LANTERN*
P5574-108 Oil Rubbed Bronze
 12" dia., 29-3/8" ht.
 Overall ht. w/ chain 68"; wire 15'.
 Four candelabra base lamps,
 each 60w max.

LARGE WALL LANTERN*
P5672-108 Oil Rubbed Bronze
 10" W., 29" ht.
 Extends 12-1/2". H/CTR 11-5/8".
 Three candelabra base lamps,
 each 60w max.

SMALL WALL LANTERN
P5670-108 Oil Rubbed Bronze
 6-1/2" W., 12-1/2" ht.
 Extends 8-3/4". H/CTR 8".
 One medium base lamp,
 100w max.

EXTRA LARGE WALL LANTERN*
P5673-108 Oil Rubbed Bronze
 12" W., 32-3/4" ht.
 Extends 14-3/4". H/CTR 14-3/4".
 Four candelabra base lamps,
 each 60w max.

**Hinged door for easy relamping.*