

Ashmore

FINISHES

- Antique Bronze - 20
- Textured Black - 31

Ashmore

P5550-20

*Handsome
Details*



Scrolled Arms

*Water
Seeded
Glass*

The Ashmore Collection features quill scrolled arms and decorative finials with etched water glass shades in a die-cast aluminum construction. This collection is ideal for illuminating new traditional and rustic settings.



P5550-20



P5550-31

POST LANTERN

P5450-20 Antique Bronze
P5450-31 Textured Black
9-5/8" dia., 23-3/4" ht.
Fits 3" post (sold separately).
Three candelabra base lamps,
each 60w max.

HANGING LANTERN

P5550-20 Antique Bronze
P5550-31 Textured Black
9-5/8" dia., 17-3/4" ht.
Overall ht. w/ chain 92"; wire 10'.
Three candelabra base lamps,
each 60w max.

FLUSH MOUNT

P5562-20 Antique Bronze
P5562-31 Textured Black
10-1/2" dia., 9-3/4" ht.
Two candelabra base lamps,
each 60w max.

SMALL WALL LANTERN

P5649-20 Antique Bronze
P5649-31 Textured Black
6-5/8" dia., 14-7/8" ht.
Extends 9-3/8". H/CTR 4-1/2".
Two candelabra base lamps,
each 60w max.

MEDIUM WALL LANTERN

P5650-20 Antique Bronze
P5650-31 Textured Black
8-5/8" dia., 16-1/2" ht.
Extends 10-3/8". H/CTR 4-1/2".
Three candelabra base lamps,
each 60w max.

LARGE WALL LANTERN

P5651-20 Antique Bronze
P5651-31 Textured Black
9-5/8" dia., 20-1/2" ht.
Extends 12-3/4". H/CTR 7".
Three candelabra base lamps,
each 60w max.

LARGE WALL LANTERN

P5652-20 Antique Bronze
P5652-31 Textured Black
8-5/8" dia., 26-1/2" ht.
Extends 12-3/8". H/CTR 19-1/8".
Three candelabra base lamps,
each 60w max.

ONE-LIGHT WALL LANTERN

P5875-20MD Antique Bronze
8-3/8" W., 16-5/8" ht.
Extends 10-1/2". H/CTR 4-1/2".
One medium base lamp,
each 100w max.



P5562-20



P5562-31



P5450-20



P5450-31



P5650-20



P5650-31



P5649-20



P5651-20



P5651-31



P5649-31



P5652-20



P5652-31



P5875-20MD