

Andover

FINISHES

- Antique Bronze - 20
- Black - 31

The Andover Collection offers a mixture of styles to complement a variety of spaces. The Black finish features an etched glass pillar diffuser inside the clear water seeded glass gives off a soft glow of light. This Andover collection is ideal for illuminating farmhouse and coastal settings.

*Die-Cast
Aluminum*

*Elegant Antique
Bronze*

Beveled Glass Panels



POST LANTERN*
P5487-20 Antique Bronze
9-1/2" sq., 21-1/2" ht.
Fits 3" post (sold separately).
Three candelabra base lamps,
each 60w max.

HANGING LANTERN*
P5587-20 Antique Bronze
9-1/2" sq., 20" ht.
Overall ht. w/chain 94"; wire 10'.
Three candelabra base lamps,
each 60w max.

MEDIUM WALL LANTERN*
P5688-20 Antique Bronze
7-1/2" W., 21-1/4" ht.
Extends 8-1/4". H/CTR 7-1/2".
Two candelabra base lamps,
each 60w max.

**Hinged door for easy relamping.*



P5587-20



P5688-20



P5487-20



P5687-20



P5689-20



P5627-20



P6619-31CD



P6620-31MD



P6621-31MD

Andover

SMALL WALL LANTERN
P5687-20 Antique Bronze
5-1/2" W., 12-3/4" ht.
Extends 6-1/4". H/CTR 6-1/4".
One medium base lamp,
100w max.

LARGE WALL LANTERN*
P5689-20 Antique Bronze
9-1/2" W., 26-1/4" ht.
Extends 10-1/4". H/CTR 9".
Three candelabra base lamps,
each 60w max.

EXTRA LARGE WALL LANTERN*
P5627-20 Antique Bronze
12-1/2" W., 34-1/2" ht.
Extends 13-1/2". H/CTR 11-3/4".
Four candelabra base lamps,
each 60w max.

SMALL WALL LANTERN
P6619-31CD Black
5-5/8" W., 13-3/8" ht.
Extends 6-3/8". H/CTR 6-3/8".
One candelabra base lamp,
60w max.

MEDIUM WALL LANTERN
P6620-31MD Black
7-1/2" W., 18-3/8" ht.
Extends 8-3/8". H/CTR 10-1/2".
One medium base lamp,
100w max.

LARGE WALL LANTERN
P6621-31MD Black
9-1/2" W., 26-1/8" ht.
Extends 10-1/4". H/CTR 12-3/4".
One medium base lamp,
100w max.

**Hinged door for easy relamping.*