

Welbourne

Hexagonal cast aluminum framework with vine-inspired scrolls. Beveled clear glass panels in Textured Black or Textured White finishes.

FINISHES

- Textured White - 30
- Textured Black - 31

POST LANTERN

P5482-30 Textured White
P5482-31 Textured Black
 9-1/2" dia., 21-1/4" ht.
 Fits 3" post (sold separately).
 One medium base lamp,
 100w max.

LARGE POST LANTERN

P5483-31 Textured Black
 13" dia., 26" ht.
 Fits 3" post (sold separately).
 Three candelabra base lamps,
 60w max.

HANGING LANTERN

P5582-30 Textured White
P5582-31 Textured Black
 9-1/2" dia., 15" ht.
 Overall ht. w/ chain 51"; wire 10'
 One medium base lamp,
 100w max.



P5682-30



P5582-30



P5582-31



P5682-31



P5681-31



P5681-30



P5482-30



P5482-31



P5683-31



P5684-31
shown without tail



P5483-30



P5483-31



P5690-31



P5684-31
shown with tail

Welbourne

SMALL WALL LANTERN

P5681-30 Textured White
P5681-31 Textured Black
 6-1/2" W., 16-7/8" ht.
 Extends 9-1/4". H/CTR 13-1/4".
 One medium base lamp,
 100w max.

SMALL WALL LANTERN

P5682-30 Textured White
P5682-31 Textured Black
 6-1/2" W., 13-1/4" ht.
 Extends 9". H/CTR 3-1/2".
 One medium base lamp,
 100w max.

MEDIUM WALL LANTERN

P5684-31 Textured Black
 Use with or without tail.
 9-1/2" W., 30-3/4" ht.
 with tail. 23-1/4" ht. without tail.
 Extends 11-3/8". H/CTR 18-3/8"
 One medium base lamp,
 100w max.

LARGE WALL LANTERN

P5690-31 Textured Black
 13" W., 22-1/4" ht.
 Extends 14". H/CTR 5".
 Three candelabra base lamps,
 each 60w max.

MEDIUM WALL LANTERN

P5683-31 Textured Black
 9-1/2" W., 18" ht.
 Extends 9-3/4" H/CTR 8-1/2".
 One medium base lamp,
 100w max.