

Brassguard® Lanterns

Unique, clear lacquer applied for long-lasting finish. All-brass construction includes protective gasket to reduce staining on siding. Black fixtures utilize aluminum construction with clear lacquer coating.

FINISHES

- Brushed Nickel - 09
- Polished Brass - 10
- Black - 31

MEDIUM HANGING LANTERN

P5834-10 Polished Solid Brass
Chain and ceiling mounts included.
7" dia., 10" ht.
Overall ht. w/chain 39-1/2"; wire 10'.
1 medium base lamp,
100w max.

LARGE POST LANTERN

P5432-10 Polished Solid Brass
P5432-31 Black
9-1/2" dia., 21" ht.
Fits 3" post (sold separately).
Three candelabra base lamps,
each 60w max.

LARGE WALL LANTERN

P5730-10 Polished Solid Brass
9-1/2" W., 26" ht.
Extends 9-1/2". H/CTR 20-1/4".
Three candelabra base lamps,
each 60w max.

MEDIUM WALL LANTERN

P5832-10 Polished Solid Brass
7" W., 14-1/4" ht.
Extends 7". H/CTR 5-3/8".
One medium base lamp,
100w max.

MEDIUM POST LANTERN

P5430-10 Polished Solid Brass
7" dia., 17" ht.
Fits 3" post (sold separately).
One medium base lamp,
100w max.



P5834-10



P5834-10
shown as semi-flush



P5730-10



P5832-10



P5430-10



P5432-10



P5432-31



P5756-10



P5756-09



P5846-31



P5756-31



P5731-31



P5831-31



P5758-31

Brassguard® Lanterns

SMALL WALL LANTERN

P5756-09 Brushed Nickel
P5756-10 Polished Solid Brass
P5756-31 Black
Open bottom.
5-1/2" W., 10-1/4" ht.
Extends 5-3/4". H/CTR 3-3/4".
One medium base lamp,
100w max.

SMALL WALL LANTERN

P5758-31 Black
5-1/2" W., 18-3/4" ht.
Extends 5-5/8". H/CTR 7-1/4".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P5831-31 Black
7" W., 29" ht.
Extends 6-3/4". H/CTR 15-3/8".
One medium base lamp,
100w max.

SMALL WALL LANTERN

P5846-31 Black
5-1/4" W., 14-3/4" ht.
Extends 6". H/CTR 8-3/8".
One medium base lamp,
60w max.

LARGE WALL LANTERN

P5731-31 Black
9-1/2" W., 35" ht.
Extends 9-1/2". H/CTR 20-1/4".
Three candelabra base lamps,
each 60w max.