

# Bulkheads LED

Robust and energy efficient, LED bulkheads are a general-purpose luminaire. Comprised of a die-cast aluminum frame and polycarbonate diffuser. Fixtures are impact resistant and offer various mounting options and can be widely adopted for indoor and outdoor applications.

## OVAL WALL OR CEILING

**P3647-3030K9** White  
**P3647-3130K9** Black  
 6-1/2" W., 10-1/2" ht.  
 Extends 4-3/8". H/CTR 5-1/4".  
 One 9w LED module, 3000K, 90CRI, 623 source lumens.

## ROUND WALL OR CEILING

**P3648-3030K9** White  
**P3648-3130K9** Black  
 9-1/2" dia., 4-3/8" ht.  
 H/CTR 4-3/4".  
 One 17w LED module, 3000K, 90CRI, 623 source lumens.

## OVAL WALL OR CEILING

**P3649-3030K9** White  
**P3649-3130K9** Black  
 6-1/2" W., 10-1/2" ht.  
 Extends 4-1/2". H/CTR 5-1/4".  
 One 9w LED module, 3000K, 90CRI, 623 source lumens.

## ROUND WALL OR CEILING

**P3650-3030K9** White  
**P3650-3130K9** Black  
 9-1/2" dia., 4-1/2" ht.  
 H/CTR 4-3/4".  
 One 9w LED module, 3000K, 90CRI, 623 source lumens.

All fixtures:



P3647-3030K9  
shown wall-mounted



P3647-3130K9  
shown ceiling-mounted



P5706-30



P3649-3130K9  
shown wall-mounted



P3649-3030K9  
shown ceiling-mounted



P5704-30



P5705-30



P3648-3130K9  
shown wall-mounted



P3648-3030K9  
shown ceiling-mounted



P5702-30



P5703-30



P3650-3130K9  
shown wall-mounted



P3650-3030K9  
shown ceiling-mounted



P3706-31  
shown ceiling-mounted



P3709-30  
shown wall-mounted



P3709-31  
shown ceiling-mounted



P3706-30  
shown wall-mounted

# Polycarbonate Bulkheads

Virtually maintenance free fixtures. Install on ceilings or walls. Classic white details and trim, Corrosion, impact and shatter resistant, UV stabilized.

## ROUND WALL OR CEILING

**P5702-30** White  
 10" dia.,  
 Extends 4-3/4".  
 One medium base lamp,  
 75w max.

## ROUND WALL OR CEILING

**P5703-30** White  
 With grill.  
 10-3/8" dia.,  
 Extends 5-7/8".  
 One medium base lamp,  
 75w max.

## OVAL WALL

**P5704-30** White  
 10-1/2" L., 5-5/8" W.  
 Extends 3-3/4".  
 One medium base lamp,  
 60w max.



## OVAL WALL

**P5705-30** White  
 With grill.  
 10-1/2" L., 5-7/8" W.  
 Extends 4".  
 One medium base lamp,  
 60w max.



## OVAL WALL

**P5706-30** White  
 Hooded.  
 10-1/2" L., 5-7/8" W.  
 Extends 4-1/8".  
 One medium base lamp,  
 60w max.

# Bulkheads

Die-cast aluminum with clear glass lens.

## OVAL WALL OR CEILING

**P3706-30** White  
**P3706-31** Black  
 6-3/8" W., 11" ht.  
 Extends 5". H/CTR 5-1/2".  
 One medium base lamp,  
 100w max.

## ROUND WALL OR CEILING

**P3709-30** White  
**P3709-31** Black  
 7-7/8" dia., 4-1/2" ht.  
 H/CTR 4".  
 One medium base lamp,  
 60w max.