

# Arlo

P250026-009-30  
shown with Brushed Nickel blades

## FINISHES


- Brushed Nickel - 009
- Black - 031
- Architectural Bronze - 129

Unwind under the cooling breeze created by the clean, crisp blades of the Arlo Collection's modern ceiling fan. A central LED light provides a perfect way to light a space without flooding the room with harsh light as six metal blades attach to the fan's center. Offered in three different finishes, Arlo is sure to create an intriguing, yet serene retreat in whatever space it calls home.

*Modern Design*

*Clean Metal Blades*

*LED Light*



P250026-009-30  
shown with Brushed Nickel blades




P250026-031-30  
shown with Black blades



P250026-129-30  
shown with Architectural Bronze blades

# Arlo

P250026-009-30 Brushed Nickel



P250026-031-30 Black



P250026-129-30 Architectural Bronze



## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	7,558 cubic feet per minute
<b>Electricity Use</b>	29 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	282 CFM/W



Full Function Remote Control Included  
Six-speed fan operation  
Full-range dimming for light  
Reverse direction control

## FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Aluminium blades
- White Opal glass
- Remote control with batteries is included

## SIZE

60" dia., 18-1/2" ht.  
80" lead wires.

## LAMP

24w LED Module, 3000K, 90 CRI,  
2000 lumens, dimmable.

