

Bixby

FINISHES

- White - 030
- Black Chrome - 231

P250038-031-30
shown with Black Smoked Translucent blades

You'll find the time to unwind under the eye-pleasing, urban industrial design of the Bixby collection's ceiling fan. Breathe easy after a warm summer day or a long day at work as Bixby fosters a refreshing current of cool air with three, slightly curved Lucite blades circling a gentle LED light as it provides soothing illumination.

Industrial Style

*Slightly Curved
Lucite Blades*


LED Light

Bixby

P250038-030-30 White

 Milk Washed Clear

P250038-231-30 Black Chrome

 Black Smoked Translucent



ENERGY INFORMATION AT HIGH SPEED

Airflow	6,846 cubic feet per minute
Electricity Use	32 watts (excludes lights)
DOE Weighted CFM/W	228 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Polycarbonate blades
- White Opal glass
- Remote control with batteries is included

SIZE

60" dia., 15-1/8" ht.
80" lead wires.

LAMP

24w LED Module,
3000K, 90 CRI,
2000 lumens, dimmable.

