

Gaze

P2554-0930K
shown with Silver blades

FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15
- Antique Bronze - 20
- Black - 31

Three-blade 60" Gaze ceiling fan features an LED light source, offering both form and function with energy and cost-savings benefits. An opal white shade contains an 18W dimmable, 3000K LED module. Gaze features a dual mount system and includes a three-speed remote control with full range dimming.

Dual Mount System

Dimmable LED Module

White Opal Shade



P2554-0930K
shown with Silver blades



P2554-1530K
shown with White Washed blades




P2554-2030K
shown with Cherry blades




P2554-3130K
shown with Matte Black blades

Gaze


P2554-0930K Brushed Nickel




P2554-1530K Polished Chrome



P2554-2030K Antique Bronze



P2554-3130K Black



ENERGY INFORMATION AT HIGH SPEED

Airflow	5,902 cubic feet per minute
Electricity Use	75 watts (excludes lights)
DOE Weighted CFM/W	87 CFM/W

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- White shatterproof lens
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

60" dia., 13-1/8" ht.
80" lead wires.



Three-Speed Remote Control Included
Three-speed fan operation
Full-range dimming for light