

# Trevina II 44"

The Trevina Collection features fans with a signature three-blade design. Perfect for modern or traditional interiors, each fan includes an LED light source to help extend your day into the evening as you and your family relax in your peaceful retreat.

## FINISHES


- Brushed Nickel - 09
- Satin White - 28
- Black - 31

**P2555-0930K** Brushed Nickel



Silver

**P2555-2830K** Satin White



White

**P2555-3130K** Black



Black

Distressed Ebony



P2555-0930K  
shown with Silver blades



P2555-2830K  
shown with White blades



P2555-3130K  
shown with Distressed Ebony blades



P2668-09



P2668-28



P2668-31

## BLANK PLATE

- P2668-09** Brushed Nickel
- P2668-28** Satin White
- P2668-31** Black

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	4306 cubic feet per minute
<b>Electricity Use</b>	42 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	122 CFM/W

## FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20")
- AC Motor
- Reversible MDF blades
- White Opal glass
- Compatible with remote or hardwired wall controls (P2630, P2661-01, P2662-01, P2663-01, P2665 (sold separately))

## SIZE

44" dia., 15-5/8" ht.  
80" lead wires.

## LAMP

18w LED Module,  
3000K, 90 CRI,  
1400 lumens, dimmable.



Wall Control Included  
Four-speed fan operation  
Full-range dimming for light  
Includes switch plate cover

# Trevina II 52"

## FINISHES

- Architectural Bronze - 129
- Painted Nickel - 152

**P2553-129WB** Architectural Bronze



Medium Cherry  
Classic Walnut

**P2553-152WB** Painted Nickel



Black  
Silver



P2553-129WB  
shown with Medium Cherry blades



P2553-152WB  
shown with Black blades

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	5,296 cubic feet per minute
<b>Electricity Use</b>	56 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	112 CFM/W

## FEATURES

- Limited lifetime warranty (LED model)
- Dual Mount (flat or sloped ceiling-30")
- AC Motor
- White opal glass
- Reversible plywood blades
- Compatible with remote control or hardwired wall controls (P2618-01, P2630, P2662-01 (sold separately))

## SIZE

52" dia., 15-3/4" ht.  
80" lead wires.

## LAMP

Two 9.5w LED lamps,  
no switch included.



P2556-3030K  
shown with White blades



P2556-2030K  
shown with Medium Cherry blades



P2556-0930K  
shown with Silver blades

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	4,916 cubic feet per minute
<b>Electricity Use</b>	62 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	89 CFM/W

## FEATURES

- Limited lifetime warranty (LED model)
- Dual Mount (flat or sloped ceiling-30")
- AC Motor
- White opal glass
- Reversible plywood blades

## SIZE

52" dia., 15-3/4" ht.  
80" lead wires.

## LAMP

17w LED Module,  
3000K, 90 CRI, 1400  
lumens, dimmable.



Wall Control Included  
Four-speed fan operation  
Full-range dimming for light  
Includes switch plate cover

# Trevina II 52"

## FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- White- 030

**P2556-3030K** White



White



Natural Cherry

**P2556-2030K** Antique Bronze



Medium Cherry

Classic Walnut

**P2556-0930K** Brushed Nickel



Silver