

Signature Plus II

Five-blade 54" Signature Plus II ceiling fan features an integrated LED light source, offering both form and function with energy and cost-savings benefits. The light kit contains a white opal shatterproof shade and is comprised of a 17W dimmable 3000K LED module.

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- White - 30

P2539-0930K Brushed Nickel

- Driftwood
- Silver

P2539-2030K Antique Bronze

- Classic Walnut
- Medium Cherry

P2539-3030K White

- White
- White



Signature Plus

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- White - 30

P2530-09 Brushed Nickel

- Natural Cherry
- Silver

P2530-20 Antique Bronze

- Classic Walnut
- Medium Cherry

P2530-30W White

- White
- White



ENERGY INFORMATION AT HIGH SPEED

Airflow	5,331 cubic feet per minute
Electricity Use	65 watts (excludes lights)
DOE Weighted CFM/W	92 CFM/W



Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited lifetime warranty
- 45° Canopy
- Downrod mount only
- AC Motor
- Reversible MDF blades
- Opal shatterproof shade
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

54" dia., 15-1/2" ht.
80" lead wires.

LAMP

17w LED Module, 3000K, 90 CRI,
1400 lumens, dimmable.



ENERGY INFORMATION AT HIGH SPEED

Airflow	4,716 cubic feet per minute
Electricity Use	65 watts (excludes lights)
DOE Weighted CFM/W	84 CFM/W

FEATURES

- 30-year limited warranty
- 45° Canopy
- Downrod mount only
- AC Motor
- Compatible with universal light kits
- Three speed pull-chain switch
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control

SIZE

54" dia., 15" ht.
80" lead wires.

