

# Alfresco

## FINISHES

- Architectural Bronze - 129
- Blistered Iron - 171

P250034-129-WB  
shown with Dark Bamboo blades

Infuse a warm, nature-inspired style to your outdoor home décor with the one-of-a-kind Alfresco Collection. Five blades decorated in a leaf-like design sprout from a dual mount center that artistically harbors an LED light source. Select from an architectural bronze and blistered iron finish to bring your bohemian dreamland to life.

*Leaf-like Decorated Blades*

*Nature-Inspired Design*

*LED Light*

# Alfresco

**P250034-129-WB** Architectural Bronze

 Dark Bamboo

**P250034-171-WB** Blistered Iron

 Pewter



P250034-129-WB  
shown with Dark Bamboo blades



P250034-171-WB  
shown with Pewter blades

## ENERGY INFORMATION AT HIGH SPEED

**Airflow** 5,724 cubic feet per minute  
**Electricity Use** 68 watts (excludes lights)  
**DOE Weighted CFM/W** 90 CFM/W



Three-Speed Remote Control Included  
*Three-speed fan operation*  
*Full-range dimming for light*

## FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- ABS blades
- Clear Seeded glass
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

## SIZE

54" dia., 19-1/4" ht.  
 80" lead wires.

## LAMP

Two ST19 vintage LED lamps, 3000K, 90 CRI, 800 lumens, dimmable.

