


Rudder

FINISHES

- Satin White- 028
- Black- 031
- Architectural Bronze - 129

P250040-028-30
shown with Distressed White blades

Transform any outdoor space into a cozy country abode with the charming rustic character of the Rudder Collection. Four boat oar-inspired blades attach to a smooth center that features an LED light source for friendly illumination as needed. Available in a matte white, matte black, or architectural bronze finish, Rudder is sure to fill your favorite patio or porch with a refreshing breeze wrapped in country character.




Rudder

P250040-028-30 Satin White



P250040-031-30 Black



P250040-129-30 Architectural Bronze



ENERGY INFORMATION AT HIGH SPEED

Airflow	6,112 cubic feet per minute
Electricity Use	35 watts (excludes lights)
DOE Weighted CFM/W	188 CFM/W

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- ABS blades
- White Opal glass
- Remote control with batteries is included

SIZE

56" dia., 16-1/8" ht.
80" lead wires.

LAMP

24w LED Module,
3000K, 90 CRI,
2000 lumens, dimmable.



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control

