

Edisto

FINISHES

- Forged Black - 80
- Antique Nickel - 81
- Architectural Bronze - 129

P2596-8030K
shown with Charcoal Canvas blades



Canvas Wrapped Blades

The Edisto 54" two-blade outdoor ceiling fan combines a sleek, contemporary style with high-quality performance. A wire frame supports canvas wrapped blades that feature UV inhibitors to protect the fabric from fading in the sunlight. Three fan speeds and a reversible switch keep individuals cool in the summer and warm in the winter. A white opal glass shade contains an 18W LED module light kit, offering energy efficient and cost savings benefits.

Contemporary Style

White Opal Glass Shade



P2596-8030K
shown with Charcoal Canvas blades




P2596-8130K
shown with Oatmeal Canvas blades



P2596-12930K
shown with Mushroom Canvas blades

Edisto

P2596-8030K Forged Black



Charcoal Canvas

P2596-8130K Antique Nickel



Oatmeal Canvas

P2596-12930K Architectural Bronze



Mushroom Canvas

ENERGY INFORMATION AT HIGH SPEED

Airflow	4,371 cubic feet per minute
Electricity Use	65 watts (excludes lights)
DOE Weighted CFM/W	73 CFM/W



Three-Speed Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-18.5")
- AC Motor
- Canvas wrapped blades
- White opal glass shade
- Damp Location Rated
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

54" dia., 14-7/8" ht.
80" lead wires.

LAMP

18w LED Module,
3000K, 90 CRI,
1400 lumens, dimmable.

