


Whirl

P2574-8130K
shown with Driftwood blades

FINISHES

- Antique Bronze - 20
- Forged Black - 80
- Antique Nickel - 81

Refresh your indoor or covered outdoor living spaces with the crisp, clean style of the 60" Whirl fan. The stylish design comes in Antique Nickel, Antique Bronze and Forged Black finish options. The five-blade fan features an all weather damp location rating to accommodate a variety of settings throughout the home.



Whirl

P2574-2030K Antique Bronze



Walnut

P2574-8030K Forged Black



Toasted Oak

P2574-8130K Antique Nickel



Driftwood

ENERGY INFORMATION AT HIGH SPEED

Airflow	6,549 cubic feet per minute
Electricity Use	70 watts (excludes lights)
DOE Weighted CFM/W	106 CFM/W

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- ABS all weather blades
- White Frosted Glass Shade
- Three speed pull-chain switch (fan)
- On/off pull-chain switch (light)
- Damp Location Rated
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control

SIZE

60" dia., 15-7/8" ht.
80" lead wires.

LAMP

18w LED Module,
3000K, 90 CRI,
1400 lumens, dimmable.

