

Holland

Enjoy nothing but first-rate design inspiration with the gorgeous Holland Collection. Four simple, yet stunning blades blend style with sustainability as they anchor to a sleek, dual mount center. An integrated LED light is ready to offer a gentle glow along with the fan's refreshing breeze. With the versatility to be installed in indoor or outdoor locations, this fan will make a design statement in any modern or transitional setting.

FINISHES

- Brushed Nickel - 009
- Black- 031
- Oil Rubbed Bronze - 108

P250032-009-30 Brushed Nickel



P250032-031-30 Black



P250032-108-30 Oil Rubbed Bronze



P250032-009-30
shown with Silver blades



P250032-031-30
shown with Black blades



P250032-108-30
shown with Walnut blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	7,035 cubic feet per minute
Electricity Use	31 watts (excludes lights)
DOE Weighted CFM/W	257 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- ABS blades
- White Opal glass
- Remote control with batteries is included

SIZE

60" dia., 13-5/8" ht.
80" lead wires.

LAMP

24w LED Module, 3000K, 90 CRI,
2000 lumens, dimmable.

