

Oriole



P2592-0930K
shown with Silver blades

This 60" Oriole ceiling fan is the perfect addition to interior garages, industrial shops or commercial buildings to distribute the right amount of air and keep the space cool and comfortable. Oriole contains an integrated 18W LED module, with an optional finishing cap offering the user the choice to install with or without the light kit. A remote control is included to adjust speed and turn on/off the light or fan. A blank off plate comes standard.



P2592-3130K
shown with Black blades
and light kit removed
using blank plate

FINISHES

● Brushed Nickel - 09

● Black - 31

● Architectural Bronze - 129

P2592-0930K Brushed Nickel

 Silver

P2592-3130K Black

 Black

P2592-12930K Architectural Bronze

 Architectural Bronze



P2592-12930K
shown with Architectural Bronze blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	6,171 cubic feet per minute
Electricity Use	51 watts (excludes lights)
DOE Weighted CFM/W	132 CFM/W

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- ABS blades
- White opal glass shade
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

60" dia., 18" ht.
80" lead wires.

LAMP

18w LED Module, 3000K, 90 CRI,
1400 lumens, dimmable.



Three-Speed Remote Control Included
Three-speed fan operation
Full-range dimming for light

