

Royer

The Royer Collection's ceiling fan offers a charming, rustic look ideal for farmhouse and rustic spaces in need of a fresh breeze. Four plywood blades attach to the fixture's center by finely detailed metal arms. The crafted center is available in three finishes so you can select the perfect piece to complement your home décor.



P250010-080
shown with Distressed Ebony blades



P250010-080
shown with Matte Black blades



P250010-081
shown with Driftwood blades




P250010-081
shown with Chesnut blades

FINISHES


- Antique Nickel - 081
- Forged Black- 080

P250010-080 Forged Black



Matte Black
Distressed Ebony

P250010-081 Antique Nickel



Driftwood
Chesnut

ENERGY INFORMATION AT HIGH SPEED

Airflow	6,255 cubic feet per minute
Electricity Use	67 watts (excludes lights)
DOE Weighted CFM/W	102 CFM/W



Three-Speed Remote Control Included
Three-speed fan operation

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- Not compatible with light kit
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

60" dia., 17-7/8" ht.
80" lead wires.

