


Chapin

The Chapin Collection effortlessly unites a spacious room, creating an atmosphere that's both relaxing and reviving. Antique nickel, graphite, or oil rubbed bronze finishes complement each other with four plywood blades and a dual mount canopy for a design destined to provide a truly relaxing experience.


FINISHES

- Antique Nickel - 081
- Oil Rubbed Bronze - 108
- Graphite - 143


P250022-081 Antique Nickel



P250022-108 Oil Rubbed Bronze




P250022-143 Graphite



P250022-081
shown with Driftwood blades



P250022-108
shown with Distressed Walnut blades



P250022-143
shown with Graphite blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	6,543 cubic feet per minute
Electricity Use	81 watts (excludes lights)
DOE Weighted CFM/W	87 CFM/W

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- Compatible with universal light kits
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

54" dia., 14-1/2" ht.
80" lead wires.



Three-Speed Remote Control Included
Three-speed fan operation