



Bedwin


Recall charming, rustic lattice work with the Bedwin Collection's farmhouse-inspired ceiling fan. With three finishes to pick from and four rough hewn plywood blades circling a handsome dual mount canopy, this ceiling fan is sure to help transform any living space into a cool paradise of relaxation.



FINISHES

- Antique Nickel - 081
- Galvanized - 141
- Graphite - 143


P250024-081 Antique Nickel



P250024-141 Galvanized



P250024-143 Graphite



ENERGY INFORMATION AT HIGH SPEED

Airflow	6,044 cubic feet per minute
Electricity Use	34 watts (excludes lights)
DOE Weighted CFM/W	192 CFM/W

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Reversible plywood blades
- Compatible with universal light kits
- Remote control with batteries is included

SIZE

56" dia., 15-1/2" ht.
80" lead wires.



Full Function Remote Control Included
Six-speed fan operation
Reverse direction control

