

Soar



P2542-0930K
shown with Black blades

With a white opal shade and a 17W dimmable LED module, the 54" Soar ceiling fan offers energy and cost-savings benefits for a variety of living spaces. The four-blade fan comes with a remote control and is available in Brushed Nickel, Antique Bronze and White finishes. LED source features a 3000K-color temperature. Soar features a dual mount system and includes a remote control with batteries.

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- White - 30

P2542-0930K Brushed Nickel




Black

P2542-2030K Antique Bronze



Walnut

P2542-3030K White



White



P2542-2030K
shown with Walnut blades



P2542-3030K
shown with White blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	4,814 cubic feet per minute
Electricity Use	65 watts (excludes lights)
DOE Weighted CFM/W	83 CFM/W

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Non-reversible plywood blades
- White opal shatterproof lens
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

54" dia., 15" ht.
80" lead wires.

LAMP

17w LED Module, 3000K, 90 CRI,
1400 lumens, dimmable.



Remote Control Included
Three-speed fan operation
Full-range dimming for light

