

Harranvale

The 54" Harranvale features a design that incorporates mixed metal design details that is very popular in today's home decor. Featuring reversible blades and opal glass shade, fans are available in three finish options: Antique Bronze with Brushed Bronze accent; Graphite with Brushed Nickel accent; and White with Brushed Nickel accent. Harranvale features a dual mount system and includes a remote control with batteries.

FINISHES

- Antique Bronze - 20
- White - 30
- Graphite - 143

P2540-2030K Antique Bronze



Classic Walnut
Medium Cherry

P2540-3030K White



White
White

P2540-14330K Graphite



Graphite
American Walnut



P2540-2030K
*shown with Brushed Bronze accent
and Medium Cherry blades*



P2540-3030K
*shown with Brushed Nickel
accent and White blades*



P2540-14330K
*shown with Brushed Nickel
accent and Graphite blades*

ENERGY INFORMATION AT HIGH SPEED

Airflow	5,121 cubic feet per minute
Electricity Use	66 watts (excludes lights)
DOE Weighted CFM/W	87 CFM/W



Remote Control Included
*Three-speed fan operation
Full-range dimming for light*

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- White opal glass shade
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

54" dia., 16-3/8" ht.
80" lead wires.

LAMP

17w LED Module, 3000K, 90 CRI,
1400 lumens, dimmable.

